

SMOKE AND CLEANING FLUID

00336-0001

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

SMOKE AND CLEANING FLUID

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Smoke and cleaning fluid

1.3. Details of the supplier of the safety data sheet

Elita Modelle Klaus Kutschka

Am Galgenbuck 6

D-90613 Großhabersdorf

Telephone: +49 (0) 9105-990018

Telefax: +49 (0) 9105-990082

e-mail: info@elita.de

Contact person: Klaus Kutschka Telephone: +49 (0) 9105-990018

http://www.elita.de

Responsible for the safety data sheet: sds@gbk-ingelheim.de

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Indications of danger : Harmful

R-phrases:

Harmful: may cause lung damage if swallowed.

Repeated exposure may cause skin dryness or cracking.

GHS classification

Hazard categories:

Aspiration hazard: Asp. Tox. 1

Hazard Statements:

May be fatal if swallowed and enters airways.

2.2. Label elements

Pictograms: GHS08



Signal word: Danger

Hazardous components which must be listed on the label

Distillates (petroleum)

Hazard statements

H304 May be fatal if swallowed and enters airways.

Precautionary statements

P102 Keep out of reach of children.

P260 Do not breathe vapour.

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

P331 Do NOT induce vomiting.

P501 Dispose of contents/container to in accordance with local and national regulations.

Special labelling of certain mixtures

EUH066 Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

Vapours may form explosive mixture with air.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

SMOKE AND CLEANING FLUID

00336-0001

Chemical characterization

Preparation in aliphatic hydrocarbons

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification	
Index No	GHS classification	
REACH No		
265-149-8	Distillates (petroleum)	> 99 %
64742-47-8	Xn - Harmful R65-66	
	Asp. Tox. 1; H304	

Full text of R and H phrases: see Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove contaminated soaked clothing immediately.
If you feel unwell, seek medical advice.
Adhere to personal protective measures when giving first aid.

After inhalation

Move to fresh air in case of accidental inhalation of vapours.
In the event of symptoms refer for medical treatment.
If patient is not breathing, apply artificial respiration.

After contact with skin

Wash off immediately with plenty of water and soap for at least 15 minutes.
Consult a doctor if skin irritation persists.

After contact with eyes

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.
Seek medical treatment by eye specialist.

After ingestion

Do not induce vomiting.
Summon a doctor immediately.
Induce vomiting only upon the advice of a physician.

4.2. Most important symptoms and effects, both acute and delayed

May be fatal if swallowed and enters airways.
Repeated exposure may cause skin dryness or cracking.
Attention. Beware, danger of aspiration.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Foam, carbon dioxide (CO₂), dry chemical, water-spray.

Extinguishing media which must not be used for safety reasons

Full water jet.

5.2. Special hazards arising from the substance or mixture

Fire may produce:
Carbon monoxide and carbon dioxide.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and protective suit.

Additional information

Cool containers at risk with water spray jet.
The vapour/air mixture is explosive, even in empty, uncleaned receptacles.
Vapours are heavier than air and spread along ground.
Do not release chemically contaminated water into drains, soil or surface waters. Sufficient measures must be taken to

SMOKE AND CLEANING FLUID

00336-0001

retain water used for extinguishing.

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

In case of vapour formation use respirator.

Use only explosion-proof equipment.

Ensure adequate ventilation.

Remove persons to safety.

Use personal protective clothing.

6.2. Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

Do not discharge into the subsoil/soil.

6.3. Methods and material for containment and cleaning up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder).

Shovel into suitable container for disposal.

Clean contaminated surface thoroughly.

6.4. Reference to other sections

Observe protective instructions (see Sections 7 and 8).

Information for disposal look up chapter 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Keep container tightly closed.

Vapours are heavier than air and spread along ground.

Avoid contact with the skin and the eyes.

Do not breathe vapours.

In case of insufficient ventilation, especially in confined areas.

Advice on protection against fire and explosion

Do not smoke - volatile.

Keep away from heat and sources of ignition.

Take precautionary measures against static discharges.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed in a dry, cool and well-ventilated place.

Pay attention to anti-explosion rules.

Advice on storage compatibility

Incompatible with:

Acids and bases.

Strong oxidizing agents

Further information on storage conditions

Keep away from food, drink and animal feeding stuffs.

7.3. Specific end use(s)

Smoke and cleaning fluid

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.2. Exposure controls

Occupational exposure controls

Ensure adequate ventilation, especially in confined areas.

Protective and hygiene measures

Do not inhale vapours.

Wash hands before breaks and immediately after handling the product.

When using, do not eat, drink or smoke.

SMOKE AND CLEANING FLUID

00336-0001

Take off immediately all contaminated clothing.

Avoid contact with skin, eyes and clothing.

Respiratory protection

In case of insufficient ventilation wear suitable respiratory equipment (gas filter type A).

Hand protection

Protective gloves resistant to chemicals made of nitrile, minimum coat thickness 0.4 mm, permeation resistance (wear duration) approx. 480 minutes, i.e. protective glove <Camatril Velours 730> made by www.kcl.de.

This recommendation refers exclusively to the chemical compatibility and the lab test conforming to EN 374 carried out under lab conditions.

Requirements can vary as a function of the use. Therefore it is necessary to adhere additionally to the recommendations given by the manufacturer of protective gloves.

Eye protection

Tightly fitting goggles.

Eye wash bottle with pure water.

Skin protection

Light protective clothing

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Colourless, clear
Odour:	Hydrocarbon-like

Test method

Changes in the physical state

Melting point:	< - 50 °C
Boiling point:	185 - 213 °C
Flash point:	62 °C

Explosive properties

The product is considered non-explosive; nevertheless explosive vapour/air mixture can be generated.

Lower explosion limits:	0,5 vol. %
Upper explosion limits:	6,5 vol. %
Ignition temperature:	210 °C
Vapour pressure:	4 hPa
(at 20 °C)	
Density (at 20 °C):	0,77 g/cm ³
Water solubility:	20 g/L
(at - 1 °C)	
Solvent content:	< 100 %

SECTION 10: Stability and reactivity

10.1. Reactivity

No decomposition if stored and applied as directed.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Reactions with acids, alkalies and oxidizing agents.

10.4. Conditions to avoid

To avoid thermal decomposition, do not overheat.

Vapour/air mixtures are explosive at intensive warming.

Heating can release vapours which can be ignited.

10.5. Incompatible materials

Strong oxidizing agents

Acids and bases.

SMOKE AND CLEANING FLUID

00336-0001

10.6. Hazardous decomposition products

Carbon monoxide and carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

No toxicological data available.

Irritation and corrosivity

Skin irritation: Not classified.

Eye irritation: Not classified.

Sensitising effects

Not classified.

Severe effects after repeated or prolonged exposure

STOT - Single exposure: Not classified.

STOT - Repeated exposure: Not classified.

Aspiration hazard: May be fatal if swallowed and enters airways.

Carcinogenic/mutagenic/toxic effects for reproduction

Carcinogenicity: Not classified.

Mutagenicity: Not classified.

Teratogenicity: Not classified.

Additional information on tests

Classification in compliance with the assessment procedure specified in the Regulation (EC) no 1272/2008.

Empirical data on effects on humans

Repeated exposure may cause skin dryness or cracking.

Contact with eyes may cause irritation.

Repeated or prolonged exposure may cause skin irritation and dermatitis, due to degreasing properties of the product.

High concentration of vapours may cause irritation to eyes and respiratory system and produce narcotic effects .

Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting.

Hazard of lung oedema. Attention. Beware, danger of aspiration!

SECTION 12: Ecological information

12.1. Toxicity

Ecological data are not available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

According to Regulation (EC) No 1907/2006 (REACH) none of the substances, contained in this product are a PBT / vPvB substance.

12.6. Other adverse effects

Low hazard to waters.

Further information

Do not flush into surface water or sanitary sewer system.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Where possible recycling is preferred to disposal.

Can be incinerated, when in compliance with local regulations.

Waste disposal number of waste from residues/unused products

SMOKE AND CLEANING FLUID

00336-0001

200129 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); detergents containing dangerous substances
Classified as hazardous waste.

Contaminated packaging

Contaminated packaging should be emptied as far as possible and after appropriate cleansing may be taken for reuse.
Packaging that cannot be cleaned should be disposed of like the product.
Empty containers should be taken for local recycling, recovery or waste disposal.

SECTION 14: Transport information

Other applicable information

No hazardous material as defined by the transport regulations.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

1999/13/EC (VOC): 100 %

National regulatory information

Employment restrictions: Observe employment restrictions for young people. Observe employment restrictions for child bearing mothers and nursing.

Water contaminating class (D): 1 - slightly water contaminating

15.2. Chemical safety assessment

For this substance a chemical safety assessment has not been carried out.

SECTION 16: Other information

Full text of R phrases referred to under Sections 2 and 3

65 Harmful: may cause lung damage if swallowed.
66 Repeated exposure may cause skin dryness or cracking.

Full text of H statements referred to under Sections 2 and 3

H304 May be fatal if swallowed and enters airways.

Further Information

Data of items 4 to 8, as well as 10 to 12, do partly not refer to the use and the regular employing of the product (in this sense consult information on use and on product), but to liberation of major amounts in case of accidents and irregularities.
The information describes exclusively the safety requirements for the product(s) and is based on the present level of our knowledge.

The delivery specifications are contained in the corresponding product sheet.

This data does not constitute a guarantee for the characteristics of the product(s) as defined by the legal warranty regulations.

(n.a. = not applicable; n.d. = not determined)

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)