



Material Safety Data Sheet

1. Product & Company Identification

Product:	3 V Lithium rechargeable battery (CR123)
Manufacturer:	Conrad Electronic SE
Nominal voltage:	3 V
Nominal capacity:	650 mAh
Address:	Klaus-Conrad-Str. 1, D-92240 Hirschau
Telephone:	+49 (0) 9604 / 40 - 8988
Date of issue:	12.03.2014

2. Composition/Information on Ingredients

Ingredient	Percent	CAS Index No./EC No.	Molecular formula
Lithium cobaltate	28.4%	12190-79-3	LiCoO ₂
Graphite	17.1%	7782-42-5	C
Electrolytes	13.2%	RR-14099-8	
Polypropylene	2%	9003-07-0	
Steel	31.1%	7439-89-6	Fe
Copper	5.7%	7440-50-8	Cu
Aluminium	2.5%	7429-90-5	Al

Weight of metallic lithium per cell: 0g. There is no metallic lithium in the lithium-ion battery.

The battery is with a watt-hour rating <= 20Wh/cell, <= 100Wh/battery pack.

3. Hazards Identification

Health Hazards (acute and chronic):

For the battery cell, chemical materials are stored in a hermetically sealed can, designed to withstand temperatures and pressures encountered during normal use. As a result, during normal use, there is no physical danger of ignition or explosion and chemical danger of hazardous materials leakage.

However, if exposed to a fire, added mechanical shocks, decomposed, or added electric stress by misuse the cell case will be breached and hazardous materials may be released. Moreover, if heated strongly by the surrounding fire, acrid gas may be emitted.

Carcinogenicity:

NTP: None

IARC Monograph: None

OSHA Regulated: None

Medical Conditions Generally Aggravated by Exposure:

An acute exposure will not generally aggravate any medical condition.



Material Safety Data Sheet

Human health effects:

Inhalation

The steam of the electrolyte has an anesthesia action and stimulates a respiratory tract.

Skin contact

The steam of the electrolyte stimulates a skin. The electrolyte skin contact causes a sore and the stimulation on the skin.

Eye contact

The steam of the electrolyte stimulates eyes. The electrolyte eye contact causes a sore and the stimulation on the eye. Inflammation of the eyes may occur.

Environmental effects

Since a battery cell remains in the environment, do not throw out it into the environment.

Specific hazards:

If the electrolyte contacts with water, it may generate detrimental hydrogen fluoride.

Since the leaked electrolyte is inflammable liquid, do not bring close to fire.

4. First Aid Measures

After inhalation contact:

Make the victim blow his/her nose, gargle. Seek medical attention if necessary.

After skin contact:

Remove contaminated clothes and shoes immediately. Immediately wash extraneous matter or contact region with soap and plenty of water.

After eye contact:

Do not rub eyes: Immediately flush eyes with water continuously for at least 15 minutes. Seek medical attention.

After ingestion contact:

Make the victim vomit. Immediately seek medical attention.

5. Fire Fighting Measures

Extinguishing Media:

Plenty of water, CO₂ gas, nitrogen gas, chemical powder, fire extinguishing medium and fire foam.

Specific methods of fire-fighting:

When the battery burns with other combustibles simultaneously, take fire extinguishing method which corresponds to the combustibles. Extinguish a fire from the windward as much as possible.

Flammable limits:

Not available.



Material Safety Data Sheet

6. Accidental Release Measure

The preferred response is to leave the area and allow the batteries to cool and the vapors to dissipate. Avoid skin and eye contact or inhalation of vapors. Remove spilled liquid with absorbent and incinerate.

7. Handling and Storage

Avoid mechanical or electrical abuse. Batteries may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity.

8. Exposure Controls/Personal Protection

Respiratory protection (Specify Type):	Not necessary under conditions of normal use.
Ventilation:	Not necessary under conditions of normal use.
Protective Gloves:	Not necessary under conditions of normal use.
Eye protection:	Not necessary under conditions of normal use.
Other Protective (Clothing or Equipment):	Not necessary under conditions of normal use.

9. Physical and Chemical Properties

Appearance:

Physical state:	Solid
Form:	Cylindrical
Color:	Metallic color
Odor:	No odor
PH:	N/A
Specific temperatures:	Temperatures range changes in physical state occur.
Flash point:	N/A
Explosion properties:	N/A
Density:	N/A
Solubility:	with indication of the solvent(s): Insoluble in water.

10. Stability and Reactivity

Stability: Stable

Conditions to avoid: When cell is exposed to an external short-circuit, crushes, deformation, high temperatures above 100 degree C, it will cause heat generation and ignition. Avoid direct sunlight and high humidity.

Hazardous Decomposition or By-products: Acrid or harmful gas is emitted during fire.

Materials to avoid: Conductive materials, water, seawater, strong oxidizers and strong acids.

Hazardous polymerization will not occur.



Material Safety Data Sheet

11. Toxicological Information

Acute toxicity:

Copper:

60-100mg sized coarse particulate causes a gastrointestinal disturbance with nausea and inflammation. TDLo, hypodermic - Rabbit 375mg/kg

Organic electrolyte:

LD50, oral - Rat 2000mg/kg or more

Further toxicological information:

Aluminium:

By the long-term inhalation of coarse particulate or fume, it is possible to cause lung damage (aluminium lungs).

Graphite:

Long-term inhalation of high levels of graphite coarse particulate may cause lung disease or a tracheal disease.

12. Ecological Information

Ecotoxic effects: N/A

Further ecological data: N/A

13. Disposal Considerations

We encourage battery recycling. Our Li-Ion batteries are recyclable. Li-Ion batteries must be handled in accordance with all applicable state and federal laws and regulations.

DO NOT INCINERATE or subject battery cells to temperatures in excess of 212 °F. Such treatment can vaporize the liquid electrolyte causing cell rupture. Do not use in combination with fresh and used lithium batteries neither with other type of battery.

14. Transport Information

International transport regulations:

1. International Air Transport Association (IATA) pursuant to Packing Instruction 965-967, Section II
2. International Maritime Dangerous Goods Code (IMDG) pursuant to Special Provisions A188 and A230.
4. U.S. hazardous materials regulations pursuant to 49 CFR 173.185 and Special Provision A188.

UN-No.:

3480

IATA Packaging Instruction:

Comply with 2014 IATA regulation 55th edition

Our Li-Ion cells pass the tests defined in UN model regulation section 38.3 Cells and batteries are packed according to the requirement of 54th edition of the IATA Dangerous Goods Regulations (DGR).

If our Li-Ion cells are used to construct battery packs, the assembler of that pack is responsible to ensure the battery has been tested in accordance with the requirements contained in the UN Model Regulations, Manual of Test and Criteria, Part III, subsection 38.3.



Material Safety Data Sheet

15. Regulatory Information

N/A

16. Other Information

DISCLAIMER

The information and recommendations set forth are made in good faith and believed to be accurate as of the date of preparation. We make no warranty, expressed or implied, with respect to this information and disclaims all liabilities from reliance on it.