

		VER:
		DATE:

li-ion Cylindrical Battery Specification

□□: LIR-9V

Prepared By/Date	Checked By/Date	Approved By/Date

Customer confirmation	
Date	

Edition	Design	Reason	Approved	Date
A		First Edition		

		VER:
		DATE:

1. Scope

This specification is applied to LIR-9V Manufactured by GREAT POWER CO., LTD .

2. Product Specification Table 1

No.	Item	Rated Performance		Remark
		Typical		
1	Rated Capacity	Typical	350mAh	Standard discharge □70mA) after Standard charge
		Minimum	320mAh	
2	Nominal Voltage	8.2V		Mean Operation Voltage During Standard Discharge After Standard Charge
3	Voltage at end of Discharge	6.0V		Discharge Cut-off Voltage
4	Charging Voltage	8.4±0.1V		
5	Max Charging Voltage	8.6V		
6	AC (1KHz) Impedance New Cell Max.(mΩ)	≤500mΩ		
7	Standard charge	Constant Current 70mA Constant Voltage 8.4V 0.01 C ₅ A cut-off		Charge time : Approx 8.0h
8	Standard discharge	Constant current 70mA end voltage 6.0V		
9	Self-discharge	≤10□		After Standard Charge, at 23 □ ±2 □, stores 30 day to measure it's capacity
10	Maximum Continuous Charge Current	350mA		
11	Maximum Continuous Discharge Current	350mA		
12	Operation Temperature Range	Charge: 0~45□		60±25%R.H. Bare Cell
		Discharge: -20~60□		
13	Storage Temperature Range	Less than 1 year: -20~25□		60±25%R.H. at the shipment state
		less than 3 months: -20~40□		
14	Weight	30g(Approx)		
15	Dimension	L26.5(+0/-2)*W 17.5(+0/-2) *H 48.5(+0/-2)mm		

3. Performance And Test Conditions

3.1 Standard Test Conditions

		VER:
		DATE:

Test should be conducted with new batteries within one week after shipment from our factory and the cells shall not be cycled more than five times before the test. Unless otherwise defined, test and measurement shall be done under temperature of $20 \pm 5^\circ\text{C}$ and relative humidity of 45~85%. If it is judged that the test results are not affected by such conditions, the tests may be conducted at temperature $15 \sim 30^\circ\text{C}$ and humidity 25~85%RH.

3.2 Measuring Instrument or Apparatus

3.2.1 Dimension Measuring Instrument

The dimension measurement shall be implemented by instruments with equal or more precision scale of 0.01mm.

3.2.2 Voltmeter

Standard class specified in the national standard or more sensitive class having inner impedance more than $10\text{k}\Omega/\text{V}$

3.2.3 Ammeter

Standard class specified in the national standard or more sensitive class. Total external resistance including ammeter and wire is less than 0.01Ω .

3.2.4 Impedance Meter

Impedance shall be measured by a sinusoidal alternating current method (1kHz LCR meter).

3.3 Standard Charge\Discharge

3.3.1 Standard Charge □ Test procedure and its criteria are referred as follows:

$$0.2C_5A = 70\text{mA}$$

Charging shall consist of charging at a $0.2C_5A$ constant current rate until the cell reaches 8.4V. The cell shall then be charged at constant voltage of 8.4volts while tapering the charge current. Charging shall be terminated when the charging current has tapered to $0.01C_5A$. Charge time: Approx 8.0h, The cell shall demonstrate no permanent degradation when charged between 0°C and 45°C .

3.3.2 Standard Discharge

$$0.2C_5A = 70\text{mA}$$

Cells shall be discharged at a constant current of $0.2C_5A$ to 6.0volts @ $20^\circ \pm 5\text{C}$

3.4 Appearance

There shall be no such defect as flaw, crack, rust, leakage, which may adversely affect commercial value of battery.

3.5 Initial Performance Test

Table 2

Item	Measuring Procedure	Requirements
(1) Open-Circuit Voltage	The open-circuit voltage shall be measured within 24 hours after standard charge.	8.2V
(2) AC Impedance Resistance	The Impedance shall be measured in an alternating current method (1kHz LCR meter) after standard charge at $20 \pm 5^\circ\text{C}$.	$\leq 500\text{m}\Omega$

3.6 Temperature Dependence of Capacity (Discharge)

Cells shall be charged per 3.3.1. and discharged @ $0.2C_5A$ to 6.0 volts. Except to be discharged at temperatures per Table 3. Cells shall be stored for 3 hours at the test temperature prior to discharging and then

		VER:
		DATE:

shall be discharged at the test temperature. The capacity of a cell at each temperature shall be compared to the capacity achieved at 23 °C and the percentage shall be calculated. Each cell shall meet or exceed the requirements of Table 3.

Table 3

Discharge Temperature	-10□	0°C	23□	60□
Discharge Capacity □0.2 C ₅ A□	50%	70%	100%	100%

3.7 Cycle Life and Leakage-Proof Table 4

No.	Item	Criteria	Test Conditions
1	Cycle Life	Higher than 60% of the Initial Capacities of the Cells	Carry out 500cycle charging/ Discharging in the below condition. □ Charge: Standard Charge, per 3.3.1 □ Discharge: 70mA to 6.0V □ Rest Time between Charge/discharge: 30min. □ Temperature: 20±5□
2	Leakage-Proof	No leakage (visual inspection)	After full charge, store at 60±3□ 60±10%RH for 1month.

4. Safety Test

Item	Battery	Test Method	Requirements
------	---------	-------------	--------------

		VER:
		DATE:

	Condition		
Crush	Fresh, Fully charged	Crush between two flat plates. Applied force is about 13kN(1.72Mpa) for 30min.	No explosion, No fire
Short Circuit	Fresh, Fully charged	Each test sample battery, in turn, is to be short-circuited by connecting the (+) and (-) terminals of the battery with a Cu wire having a maximum resistance load of 0.1Ω. Tests are to be conducted at room temperature(20±2℃).	No explosion, No fire The Temperature of the surface of the Cells are lower than 150℃
Short Circuit	Fresh, Fully charged	Each test sample battery, in turn, is to be short-circuited by connecting the (+) and (-) terminals of the battery with a Cu wire having a maximum resistance load of 0.1Ω. Tests are to be conducted at temperature(60±2℃).	No explosion, No fire The Temperature of the surface of the Cells are lower than 150℃
Impact	Fresh, Fully charged	A 56mm diameter bar is inlaid into the bottom of a 10kg weight. And the weight is to be dropped from a height of 1m onto a sample battery and then the bar will be across the center of the sample.	No explosion, No fire
Forced Discharge	Fresh, Fully charged	Discharge at a current of 1C ₅ A for 2.5h.	No explosion, No fire
Nail Pricking (3mm)	Fresh, Fully charged	Prick through the sample battery with a nail having a diameter of 3mm and remain 2h.	No explosion, No fire

5. CAUTIONS IN USE

To ensure proper use of the battery please read the manual carefully before using it.

. Handling

		VER:
		DATE:

- Do not expose to, dispose of the battery in fire.
- Do not put the battery in a charger or equipment with wrong terminals connected.
- Avoid shorting the battery
- Avoid excessive physical shock or vibration.
- Do not disassemble or deform the battery.
- Do not immerse in water.
- Do not use the battery mixed with other different make, type, or model batteries.
- Keep out of the reach of children.

. charge and discharge

- Battery must be charged in appropriate charger only.
- Never use a modified or damaged charger.
- Do not leave battery in charger over 24 hours.

. storage

- Store the battery in a cool, dry and well-ventilated area.

. disposal

- Regulations vary for different countries. Dispose of in accordance with local regulations.

6 Battery operation instruction

6.1 Charging

Charging current □ Cannot surpass the biggest charging current which in this specification book stipulated □

Charging voltage □ Does not have to surpass the highest amount which in this specification book stipulated to decide the voltage □

Charge temperature □ The battery must carry on the charge in the ambient temperature scope which this specification book stipulated □

Uses the constant electric current and the constant voltage way charge, the prohibition reverse charges. If the battery positive electrode and the cathode meet instead, can damage the battery □

6.2 Discharging current

The discharging current does not have to surpass this specification book stipulation the biggest discharging current, the oversized electric current electric discharge can cause the battery capacity play to reduce and to cause the battery heat □

6.3 Electric discharge temperature

The battery discharge must carry on in the ambient temperature scope which this specification book stipulated

6.4 Over-discharges

After the short time excessively discharges charges immediately cannot affect the use, but the long time excessively discharges can cause the battery the performance, battery function losing. The battery long-term has not used, has the possibility to be able to be at because of its automatic flashover characteristic certain excessively discharges the condition, for prevented excessively discharges the occurrence, the battery should maintain the certain electric quantity □

6.5 Storing the Batteries

The battery should store in the product specification book stipulation temperature range. If has surpasses above for six months the long time storage, suggested you should carry on additional charge to the battery □

		VER:
		DATE:

7. Period of Warranty

The period of warranty is one year from the date of shipment. Great Power guarantees to give a replacement in case of cells with defects proven due to manufacturing process instead of the customers abuse and misuse.

8 Other The Chemical Reaction

Because batteries utilize a chemical reaction, battery performance will deteriorate over time even if stored for a long period of time without being used. In addition, if the various usage conditions such as charge, discharge, ambient temperature, etc. are not maintained within the specified ranges the life expectancy of the battery may be shortened or the device in which the battery is used may be damaged by electrolyte leakage. If the batteries cannot maintain a charge for long periods of time, even when they are charged correctly, this may indicate it is time to change the battery.

9. Note: Any other items which are not covered in this specification shall be agreed by both parties.

10. Initial Dimension:

VER:



DATE:

Edition NO.

Date

Sign

Checked



L	26.5+0/- 2	W	17.5+0/- 2	H	+0/-2	UNIT	mm
Drawer		Checked		Approved		Date	
				LiR-9V DRAWING			
				Drawing ID			