



VISION LFP battery

MATERLAL SAFETY DATA SHEET

VISION R & D center Issue date:2011-3-16 Ref:2009-01

LI-ION (LiFePO₄) BATTERY (UN3480)

1. PRODUCT.IDENTIFEICATION

Product name			Vision Lithium Iron Phosphate Battery	
Manufacturer			Shenzhen Center Power Tech. Co. Ltd.	
Address			Center Power Industrial Park,	
			Tongfu Industrial District Dapeng Town	
			518120 Shenzhen, China	
Electroche	e Electrodes: Negative Electrode		С	
mical		Positive Electrode	LiFePO4	
system Electrolyte			LiPF ₆	
Telephone	Telephone		+86-755-8431 8088	
Fax			+86-755-8431 8038	
E-mail			sales@vision-batt.com	
Website			http://www.vision-batt.com	

2. COMPOSITION/INFORMATION ON INGREDIENTS.

PRINCIPAL HAZARDOUS	Chamical Symphol	Weight $(0/)$	Malting Daint %	CAS No.
COMPONENT(S) (chemical and common name(s)	Chemical Symbol	Weight (%)	Melting Point °C	CAS NO.
Lithium iron phosphate	LiFePO4	23~33	> 1000	15365-14-7
Carbon	С	12~17	> 1000	7440-44-0
	EC		EC : 38 °C	
Organic solvents	PC	3	PC : -49 ℃	
Organic solvents	DEC		DEC : -43 ℃	
	LiPF6		N/A	21324-40-3
ABS	Acrylonitrile	5	175 °C	
ADS	butadiene-styrene resin	5	175 C	

COMMON NAME: (Used on label) Vision Lithium Iron Phosphate Battery

3. HAZARD DATA

3.1 Physical:

The Li-ion batteries described in this Material Safety Data Sheet are sealed which are not hazardous when used according to the recommendations of the manufacturer.

Under normal conditions of use, electrode materials and liquid electrolyte they contain are non-reactive provided the battery integrity is maintained and seals remain intact, Risk of exposure only in case of abuse, e.g. mechanical, thermal, electrical, which leads to the activation of safety valves and/or the rupture of the battery containers. Electrolyte leakage, electrode materials reaction with moisture/water of battery vent/explosion/fire may follow depending upon circumstances.

3.2 Chemical:

	Chashired on or anger out publication of containing the result of the provide the				
substance	Chemical	Indication of	Special Risk	Safety Advice	
	Symbol	Danger			
Lithium iron	LiFePO ₄		R22 R43	S2 S22	
phosphate				S24 S26 S36	
				S37 S45	
Carbon	С				
	EC	Flammable	R21 R22	S2 S24	
Organia	PC		R41	S26 S36	
Organic solvents	DEC		R42/43	S37 S45	
sorvents	LiPF ₆	Irritant	R14	S2 S8 S22	
		Corrosive		S24 S26 S36	

Classification of dangerous Substances Contained into the Product as per Directive

slight variations depending from all type

1. Name of Special Risks:

R14/15 Reacts with water and yields flammable gases

- R21 Harmful in contact with skin
- R22 Harmful us swallowed
- R35 Causes severe burns
- R41 Risk of serious damage to the eye

R42/43 May cause sensitization by inhalation and skin contact

R43 May cause sensitization by skin contact

2. Safety Advices:

- S2 Keep out of reach from children
- S8 Keep away from moisture
- S22 Do not breathe dust
- S24 Avoid contact with skin
- S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical attention
- S36 Wear suitable protective clothing
- S37 Wear suitable gloves
- S45 In case of incident, seek medical attention

4. FIST AID MEASURES

In case of battery rupture or explosion, evacuate personnel from contaminated area and provide maximum ventilation

to clear out corrosive fumes/gases and pungent odors.

In all case, seek immediate medical attention,

Eye contact:	Flush with plenty of water(eyelids-held open) for at least 15 minutes	
Skin contact:	Remove all contaminated clothing and flush affected areas with plenty of	
	water and sop for at least 15minutes.	
Ingestion:	Dilute by giving plenty of water and get immediate medical attention.	
	Assure that the victim does not aspirate vomited material by use of positional	
	drainage.	
	Assure that mucus does not obstruct the airway.	
	Do not give anything by mouth to an unconscious person	
Inhalation:	Remove to fresh air and ventilate the contaminated area.	
	Give oxygen or artificial respiration if needed.	

5. FIRE-FIGHTING MEASURES

Fire and explosion hazard:	The batteries can leak and/or spout vaporized or decomposed and combustible
	electrolyte fumes in case of exposure above 90 °C resulting from inappropriate use

	or from the environment. Possible formation of hydrogen fluoride (HF) and		
	phosphorous oxides during fire.LiPF ₆ salt contained in the electrolyte releases		
	hydrogen fluoride (HF) in contact with water.		
Extinguishing media:	Suitable : CO2,		
	Dry chemical or Foam extinguishers		
	Not to be used : Type D extinguishers		
Special exposure hazards:	Following cell overheating due to external source or due to unproper use, electrolyte		
	leakage or battery container rupture may occur and		
	release inner component/material in the environment.		
	Eye contact: The electrolyte solution contained in the battery is irritant to ocular		
	tissues.		
	Skin contact: The electrolyte solution contained in the battery causes skin		
	irritation.		
	Ingestion: The ingestion of electrolyte solution causes tissue damage to throat		
	and gastro/respiratory tract.		
	Inhalation: Contents of a leaking or ruptured battery can cause respiratory		
	tract, mucus, membrane irritation and edema.		
Special protective equipment:	Use self-contained breathing apparatus to avoid breathing irritant fumes.		
	Wear protective clothing and equipment to prevent body contact with electrolyte		
	solution.		

6. ACCIDENTAL RELEASE MEASURES

The material contained within the batteries would only be expelled under abusive conditions. Using shovel or broom, cover battery or spilled substances with dry sand or vermiculite, place in approved container (after cooling if necessary) and dispose in accordance with local regulations.

7. HAHDLING AND STORAGE

The batteries should not be opened destroyed or incinerated since they may leak or rupture and release in the environment the ingredients they contain.

Handli	Do not crush, pierce, short (+) and (-) battery terminals with conductive (i.e. metal) goods. Do not directly		
ng	t or solder. Do not throw into fire. Do not mix batteries of different types and brands. Do not mix new and		
	d batteries. Keep batteries in non-conductive (i.e. plastic) trays.		
Storage	Store in a cool (preferably below 30 °C) and ventilated area away from moisture, sources of heat, open		
	flames, food and drink. Keep adequate clearance between walls and batteries. Temperature above 90 °C may		
	result in battery leakage and rupture. Since short circuit can cause burn, leakage and rupture hazard, keep		
	batteries in original packaging until use and do not jumble them.		
Other	Manufacturer recommendations regarding maximum recommended currents and operating temperature		
	range.		
	Applying pressure on deforming the battery may lead to disassembly followed by eye, skin and throat		
	irritation.		

8. EXPOSRE CONTROLS/PERSONAL PROTECTION

Respiratory protection:	Not necessary under normal use.	
	In case of battery rupture, use self-contained full-face respiratory equipment. Equipment	
	with type ABEK filter.	
Hand protection:	Not necessary under normal use.	
	Use rubber gloves if handling a leaking or ruptured battery.	
Eye protection: Not necessary under normal use. Wear safety goggles or		
	glasses with side shields if handling a leaking or ruptured	

	battery.	
Skin protection:	Not necessary under normal use. Use rubber apron and	
	protective working in case of handling of a ruptured	
	battery.	

9. PHYSICAL AND CHEMICAL PROPERTIES

Cells are not single chemical material: there are no specific physical and chemical properties such as melting point and boiling point.

Main purpose of lithium ion cells:used in notebook computers.

10. STABILITY AND REACTIVITY

Conditions to avoid	Heat above 90 °C or incinerate. Deform, mutilate, crush, pierce, and disassemble.		
Conditions to avoid	Short circuit. Prolonged exposure to humid conditions.		
Materials to avoid	N/A		
Hazardous	Corrosive/Irritant Hydrogen fluoride (HF) is produced in case of reaction of lithium		
decomposition	(LiPF ₆) with water. Combustible vapors and formation of Hydrogen fluoride (HF) and		
products	phosphorous oxides during fire.		

11. TOXILOGICAL INFORMATION

The Li-ion batteries do not contain toxic materials

12 ECOLOGICAL INFORMATION

When properly used or disposed, the Li-ion batteries do not resent environmental hazard

13. DISPOSAL CONSIDERATION

Dispose in accordance with applicable regulations which vary from country to country.

(In more countries, the thrashing of used batteries is forbidden and the end-users are invited to dispose them properly, eventually through not-for-profit organizations, mandated by local governments or organized on a voluntary basis by professionals).

Lithium-Ion batteries should have their terminals insulated and be preferably wrapped in plastic bags prior to disposal.

13.1 Incineration: Incineration should never be performed by battery users but eventually by trained professionals in authorized facilities with proper gas and fumes treatment.

14. TRANSPORT INFORMATION

The consignment complies with the current edition-51th, 2010 of the IATA DGR.

Description: Lithium ion battery (UN3480)

1) This consignment is complying with THE Section II of PI965 of IATA DGR 51TH Ed.

2) UN manual of Tests and criteria, part III, sub-section 38.3(withstanding a 1.2m drop test)

The consignment can be shipped as "Not Restricted" in accordance with the current edition of IATA-DGR-2010. (UN3480)

A) This consignment packed in a clean, good and strong outer packaging.

B) This consignment does not contain any recalled and/or defective batteries.

C) This consignment have been packed in comply with the Section II of PI965

D) Handle with care, Flammabllity hazard exists if the package is damaged.

E) In any event of the package is fond damaged, please follow the special procedures

If package is damaged, batteries must be protected so as to prevent short circuit. Batteries are completely

enclosed by inner packaging (so) as to prevent from short circuit

F) For any additional information, please contact

+86(755)84318088(CHINA)

No	ITEMS	RESULT	REMARKS
----	-------	--------	---------

1	Altitude simulation	Pass	Test 1 to 5 must be conducted in
2	Thermal test	Pass	sequence on the same cell or battery
3	Vibration	Pass	
4	Shock	Pass	
5	External short circuit	Pass	
6	Impact	Pass	
7	Overcharge	Pass	Only battery do need this test item
8	Forced Discharge	Pass	

The product is not classified as dangerous under the current edition of the **51th,2010 of the IATA DGR.** dangerous goods regulations and according the Section II of PI965 all applicable Carriers. The product is safe for air transportation and not regulated by IATA DGR.

products had been passed UN38.3 Test & declare that the lithium battery are not restricted & complied to Secti on II of PI965 - PI970.

15. REGULATORY INFORMATION

These is no regulation on Lithium batteries management.

16. OTHER INFORMATION/DISCLAIMER

This information has been compiled from sources considered to be dependable and is, to the best of our knowledge and belief, accurate and reliable as of the date compiled. However, no representation, warranty (either expressed or implied) or guarantee is made to the accuracy, reliability or completeness of the information contained herein.

This information relates to the specific materials designated and may not be valid for such material used in combination with any other materials or in any process. It is the user's responsibility to satisfy himself as to the suitability and completeness of this information for his particular use.

B&K does not accept liability for any loss or damage that may occur, whether direct, indirect, incidental or consequential, from the use of this information. B&K does not offer warranty against patent infringement. Additional information is available by calling the telephone number above designated purpose.