

ICP581323PA

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V
Safety Circuit

Specifications

Renata Type	ICP581323
IEC Designation	ICP071425
Part Number	100692
Contact Method:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	145 mAh
Minimum Capacity	140 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 410 mΩ / 50% SOC

Thickness (t)	Max 6.2 mm
Length (l)	Max 24.5 mm
Width (w)	Max 13.2 mm
Weight	~ 3.7 g

Charging Characteristic

Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 72.5 mA
Max. Charging Current	1.0 C CC – 145 mA
Temperature at Charging	0 °C 45 °C


Discharge Characteristic

Cut off Voltage	3.0 V
Max discharge Current	2.0 C – 290 mA (for non continues discharge) 1.0 C – 145 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. Li Ion ICP581323 – 11.09