

ICP402050PR

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V
Safety Circuit

Specifications

Renata Type	ICP402050
IEC Designation	ICP052153
Part Number	100649
Contact Method	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	420 mAh
Minimum Capacity	400 mAh (0.2C cut off 3.0 V at 20 °C)

Internal Impedance	< 290 mΩ / 50% SOC
--------------------	--------------------

Thickness (t)	Max 4.5 mm
Length (l)	Max 52.5 mm
Width (w)	Max 20.7 mm
Weight	~ 8.8 g

Charging Characteristic

Voltage	CC/CV – Constant Current / Constant Voltage 4.2 V CV
Current Normal	0.5 C CC – 210 mA
Max. Charging Current	1.0 C CC – 420 mA
Temperature at Charging	0 °C 45 °C


Discharge Characteristic

Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 840 mA (for non continues discharge) 1.0 C – 420 mA (for continues discharge)
Temperature During Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	--

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. Li Ion ICP402050 - 11.01