SAIL-M12GM12G-CD-15A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com





The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

Available until	2013-04-15
Type	SAIL-M12GM12G-CD-15A
Order No.	1964711500
Version	Bus line, Connecting line, M12 / M12, No. of poles: 5, 15 m, pin, straight - socket, straight, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4050118006032
Qty.	1 pc(s).

SAIL-M12GM12G-CD-15A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	937 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Technical specifications for cable

Number of poles	5	Wire cross section	2 x 0.34 mm² + 2 x 0.22 mm²
Outside diameter	7 ± 0.3 mm	Cable length	15 m
Shielded	Yes	Insulation	TPE
Colour coding	white, blue, red, black	Sheath material	PUR
Sheathing colour	black	Halogen	No
Temperature range, moving	-10...80 °C	Temperature range, stationary	-40...80 °C
Outer cladding in accordance with UL AWM style	20236 (80 °C / 30 V)	Suitable for cable carriers	Yes
Bending radius, min., stationary	5 x cable diameter	Bending radius, min., moving	10 x cable diameter
Acceleration	5 m/s²	Speed	180 m/min
Bending cycles	3 Mio	Resistant to welding beads	No
Hybrid cable	No	Irradiation crosslinked	No
Configurable cable length	No		

General technical data

Version	pin, straight - socket, straight	Connection thread	M12 / M12
Housing main material	PUR	Threaded ring material	Brass, nickel-plated
Coding	A	Protection degree	IP67
Contact surface	Gold-plated	LED	No
Rated voltage	125 V	Rated current	4 A
Insulation strength	10^8 Ω	Temperature range of housing	-25...+80 °C
Tightening torque	M12: 0.8 - 1.2 Nm	Plugging cycles	≥ 100
Pollution severity	3	jumpered	No

Standards

Certificate no. (cULus)	E307231

Classifications

ETIM 6.0	EC002599	eClass 6.2	27-06-03-07
eClass 7.1	27-06-03-07	eClass 8.1	27-06-03-07
eClass 9.0	27-06-03-08	eClass 9.1	27-06-03-08

Approvals

Approvals	c UL us LISTED
ROHS	Conform

Creation date May 28, 2019 12:03:49 AM CEST

SAIL-M12GM12G-CD-15A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Downloads


Brochure/Catalogue	FL FIELDWIRING EN

SAIL-M12GM12G-CD-15A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com


Drawings

Dimensioned drawing




Male, straight

Dimensioned drawing




Straight socket

Pole scheme




Pin

Pole scheme



Socket

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

Creation date May 28, 2019 12:03:49 AM CEST