

SAIB 5/9-VA-B-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

Tension-clamp connection delivers excellent functional security and reduced installation times. With this technology the conductor is plugged into the tension clamp without a wire-end ferrule (optionally with wire-end ferrule). The connection between the conductor and tension clamp is vibration-resistant and boasts long-term stability.

General ordering data

Type	SAIB 5/9-VA-B-COD
Order No.	1920730000
Version	Sockets prefabricated to customer spec., Plugs prefabricated to customer spec., M12, Female socket, straight
GTIN (EAN)	4032248561452
Qty.	1 pc(s).

SAIB 5/9-VA-B-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	50 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	6...8 mm (PG9)	Cable diameter, max.	8 mm
Cable diameter, min.	6 mm	Cable gland	PG 9
Coding	B	Connection cross-section, max.	0.5 mm ²
Connection cross-section, min.	0.14 mm ²	Contact surface	Gold-plated
Housing main material	1.4404/316L	Insulation resistance	10 ⁸ Ω
No. of poles	5	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP 69K
Rated current	4 A	Rated voltage	125 V
Rated voltage (text)	125 V (5-pole) / 60 V (8-pole)	Shield connection	Yes
Threaded ring material	Stainless steel	Type of connection	Tension clamp connection

Classifications

ETIM 3.0	EC002062	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals	
ROHS	Conform