

样品承认书

SPECIFICATION FOR APPROVEAL

客户名称 (Customer Name) :

客户料号 (Customer P/N) :

产品型号 (Model Name) : **49AA2200EH mAh**

发行日期 (Issue Date) : **2010.05.11**

APPROVED:

客户		倍特力	
确认(Checked By)		编制(Auditted By)	杨胜兰
		确认(Checked By)	钟智勇
批准(Approved By)		批准(Approved By)	叶凯
		签章 (Signature&chop)	签章 (Signature&chop)

深圳市倍特力电池有限公司

SPECIFICATIONS OF NICKEL METAL HYDRIDE BATTERY

1. APPLICATION

The applicable range: This specification is available only for the testing within one month since receipt of batteries. It's not a standard for stored goods.

Model: BPI-49AA2200EH mAh

2. RATINGS


Nominal Voltage	<u>1.2</u> V
Nominal	<u>2200</u> mAh
Minimum	<u>2160</u> mAh/0.2C
Standard charge rate	<u>220</u> mA × 16h
Rapid charge rate	<u>1100</u> mA × 140min (stop when voltage reduce to 5mV)
Value of dT/dt (for reference only)	1 to 2 °C/min
Operating temperature range	Humidity: +65% ± 20%
Standard charge	0 to +45°C
Rapid charge	0 to +40°C
Discharge	0 to +55°C
Storage temperature range	Humidity : +65% ± 20%
Within 1 year	0 to +35°C
Within 6 months	0 to +45°C
Within 1 month	0 to +55°C
Within 1 week	0 to +55°C

- Note :
- (1) Specified capacity figures are based on single cell performance.
 - (2) All rapid charge systems should be discussed with our engineer.
 - (3) We stipulate to charge only 30% fully power for delivery, while only 50% for blister with 2pcs or below, and only 30% with over 2pcs. If customer requires charged power to exceed what we stipulate, BetterPower won't be responsible for this during delivery and storage.
 - (4) shelf life: 24 months.

3. Measurement & Dimensions

to see the drawing :

D	13.8~14.5mm
H	49.0~50.0mm



4. Performance Testing

想的更多，做得更好！

Think more, do better !

4.1. TEST CONDITIONS

4.1.1 The battery to be tested is the product within one month after being received by customer.

4.1.2 Ambient conditions:

Temperature	+20°C±5°C
Humidity	+65%±20%

4.2 Testing Tools

4.2.1 Voltage meter:

0.5 level or higher as required in IEC51/IEC485. Internal impedance exceeds 10KΩ/V.

4.2.2 Current meter:

0.5 level or higher as required in IEC51/IEC485. Internal impedance should be less than 0.01Ω/V(including wires).

4-2.3. Micrometer caliper:

With precision of 0.02mm.

4-2.4. Internal impedance meter:

Alternating current of 1000HZ, connector measuring equipment with sin wave of 4.

4-2.5: Impedance loaded meter:

Value of impedance is with ±5% error allowed (including external wires).

4.2.6 Incubators Accuracy ±2°C

4.3 Test methods and benchmarks

Item	Test Method	Benchmark
1. Appearance:	✧ eyeballing	✧ batteries shall be free from any stains; scratches or deformations, which may reduce the commercial value when visually inspected
2. Size:	✧ caliper measurement.	✧ The size shall comply with the specified size as the attached drawing
3. Insulate impedance	✧ measured with a Megger overpack and battery electrode between the degree of insulation.	✧ outer sleeve shall exceed <u>10</u> MΩ.
4. Weight	✧ using disk-scale measurement.	✧ approximate <u>29.5</u> g.
5. Charge Voltage	✧ Following a period of discharge at 0.2CmA down to a terminal voltage of 1.0V, standard charge, the cell or battery shall be checked at 5 minutes before finish charging.	✧ The voltage shall be less than <u>1.6</u> V.
6. Open circuit voltage: (O.C.V.)	✧ Following a standard charge period, the open circuit voltage of the cell or battery shall be checked within 1 hour.	✧ The O.C.V. shall exceed <u>1.25</u> V per cell.
7. Closed circuit voltage: (C.C.V.)	✧ Following a standard charge period, the closed circuit voltage of the cell or battery shall be checked with a 0.86 Ω per cell load within 1	✧ The C.C.V. shall exceed <u>1.2</u> V per cell.

	hour。	
8. Internal impedance	<ul style="list-style-type: none"> Following a standard charge period, the internal impedance of the cell or battery shall be checked at 1000Hz within 1 hour。 	<ul style="list-style-type: none"> The internal impedance shall not be more than <u>32</u> mΩ per cell。
9. capacity	<ul style="list-style-type: none"> Following a standard charge period, the cell shall be stored for a period of 1 hour. The capacity shall be equal or more than minimum capacity when discharged at <u>0.2C</u> mA down to a terminal voltage of 1.0V; The capacity returned might not initially attain the specified value following the first charge –discharge cycle. In this event, the test may be repeated a further two or three times to attain the minimum capacity。 	<ul style="list-style-type: none"> The capacity is greater than or equal to the minimum capacity。
10. High Drain Discharge	<ul style="list-style-type: none"> To discharge by 0.5C to 1.0V within 1 hour after standard charge。 	<ul style="list-style-type: none"> The Capacity is higher than or equal to 114 min。
11. Over-charge	<ul style="list-style-type: none"> Following a period of discharge at <u>0.2C</u> mA down to a terminal voltage of 1.0V, standard charge and then charge for 48hrs at <u>0.1C</u> mA. The capacity of the cell or battery shall not be less than the rated capacity when discharged at <u>0.2C</u> mA。 	<ul style="list-style-type: none"> It shall not be externally deformed and no leakage of electrolyte in liquid form shall be observed。
12. Over-discharge ★★★★★	<ul style="list-style-type: none"> Following a period of discharge at <u>0.2C</u> mA down to a terminal voltage of 1.0V, combine the cells with a <u>0.86</u> Ω per cell load. After stored for a period of 24 hours, standard charged and then discharge at <u>0.2C</u> mA。 	<ul style="list-style-type: none"> the cell or battery shall not be externally deformed and no leakage of electrolyte in liquid form shall be observed, and the subsequent capacity shall not be less than <u>98%</u> of rated capacity. ★
13. Self discharge ★★★★★	<ul style="list-style-type: none"> Following a period of discharge at <u>0.2C</u> mA down to a terminal voltage of 1.0V, standard charge and then the cell or battery shall be stored for 180 days below 20°C。 	<ul style="list-style-type: none"> The subsequent capacity shall not be less than <u>85%</u> of rated capacity when discharged at <u>0.2C</u> mA。 . ★
	<ul style="list-style-type: none"> Following a period of discharge at <u>0.2C</u> mA down to a terminal voltage of 1.0V, standard charge and then the cell or battery shall be stored for 360 days below 20°C。 	<ul style="list-style-type: none"> The subsequent capacity shall not be less than <u>80%</u> of rated capacity when discharged at <u>0.2C</u> mA。 . ★

	Note: The data may be different from the above value, if the environmental temperature is changed.	
14. Cycle Life	✧ Based on clause 7.4.1.1, IEC61951-2 2003.	✧ The charge-discharge cycles shall exceed <u>500</u> times.
15. Humidity	✧ Standard charge and store for 14 days under the following storage conditions: $33^{\circ}\text{C} \pm 3^{\circ}\text{C}$ ($91.4^{\circ}\text{F} \pm 5.4^{\circ}\text{F}$), Relative humidity of $80\% \pm 5\%$. (Salting is permitted).	✧ No leakage of electrolyte in liquid form shall be observed.
16. Vibration	✧ Store the cell or battery more than 24 hours after standard charge, following vibration tests over an amplitude of 4 mm (0.1575 inches) at a frequency of 16.7 Hz(1000 cycles per minute) and repeated through any axes during 60mins.	✧ The subsequent fluctuation of open circuit voltage and internal impedance shall be less than <u>0.02</u> V and <u>5</u> m Ω respectively, and the cell or battery shall not be externally deformed and no leakage of electrolyte in liquid form shall be observed. .
17. Free falling: (Drop)	✧ Store the cell or battery more than 24 hours after standard charge, following a drop test from 450mm (17.717 inches) on to a hard-wood board in a vertical axis 2 times on each of 2 mutually perpendicular axes,	✧ The subsequent fluctuation of open circuit voltage and internal impedance shall be less than <u>0.02</u> V and <u>5</u> m Ω respectively, and the cell or battery shall not be externally deformed and no leakage of electrolyte in liquid form shall be observed..
18. Short-circuit testing	✧ to store it for 1 hour after standard charged, and to make positive and negative electrode short-circuit with a wire with the section 0.75mm ² min and shortest length, the short-circuit time is 1 hour	✧ It shall not explode during or at the end of a 1 hour short-circuit test. However, leakage of electrolyte, external deformation or outer sleeve cracking is permitted. .
19. Safty Valve Performance (Over dis-charging)	✧ to be charged with <u>1C</u> mA for 5 hours	✧ safety valve can work normally, no breakage, leakage, distortion and out package breakage are allowed
20. Safty Valve Performance (over charging)	✧ to be charged with <u>1C</u> mA for 5 hours	✧ No explosion, but leakage, distortion and out package breakage are allowed
21.To discharge at low temperature	✧ to be stored for 24 hours at $0^{\circ}\text{C} \pm 2^{\circ}\text{C}$, and discharged at <u>0.2C</u> mA at $0^{\circ}\text{C} \pm 2^{\circ}\text{C}$.	✧ discharge duration shall exceed <u>4</u> hour.

5. The transportation and storage


5-1 During transportation, it should be prevented from fierce vibration, impact ,extrusion, insulating or drenching under clean, dry and ventilated place. Applicable in transportation by automobile, train, steamboat and airplane.

5-2. It must be stored at 0 °C ~ +35 °C, and put in the clean, dry and ventilated place with relative humidity 75% max.. It must be kept away from corrodent sustance, fire hazard and heat resource.

6. Discharging and charging curves


6-1. Discharging Curves

DISCHARGE CHARACTERISTICS OF BPI-49AA2200EHmAh CELL



6-2. Charging Cureves

CHARGING CURVE OF BPI-49AA2200EHmAh CELL



7. Others:

- 7-1. BetterPower reserve right to revise the specification without notification;
- 7-2. Anything not mentioned in this specifications, customer and BetterPower should discuss to get a solution;
- 7-3. BetterPower does not undertake any responsibility for the accidents caused by actions not matching with specifications.

***** END *****