

SAIL-M8BG-4-5.0V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIL-M8BG-4-5.0V
Order No.	1927260500
Version	Sensor/actuator line, One end without connector, M8, No. of poles: 4, 5 m, Female socket, straight, shielded: No, LED: No, Sheath material: PVC, Halogen: Yes
GTIN (EAN)	4032248574988
Qty.	1 pc(s).

SAIL-M8BG-4-5.0V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technische Daten**Dimensions and weights**

Net weight	175 g
------------	-------

Technical specifications for cable

No. of poles	4	Core cross-section	0.25 mm ²
shielded	No	Insulation	PVC
Colour coding	Brown, White, Blue, Black	Sheath material	PVC
Sheathing colour	Black	Outer diameter	4.8 ± 0.2 mm
Cable length	5 m	Temperature range, moving, min.	-5 °C
Temperature range, moving, max.	80 °C	Temperature range, stationary, min.	-30 °C
Temperature range, stationary, max.	80 °C	Halogen	Yes
Suitable for cable carriers	No	Torsion resistance	0 °/m
Resistant to welding beads	No		

General technical data

Version	Female socket, straight	Contact tube diameter	M8
Housing main material	PUR	Threaded ring material	Brass, nickel-plated
Coding	none	Protection degree	IP 65, IP 66, IP 67, IP 68, (when screwed in)
Contact surface	Gold-plated	LED	No
Rated voltage	30 V	Rated current	4 A
Insulation resistance	10 ⁸ Ω	Temperature range of housing	-25...+85 °C
Tightening torque	M8: 0.5 - 0.6 Nm	Plugging cycles	≥ 100
Pollution severity	3	jumpered	No

Classifications

ETIM 3.0	EC001855	UNSPSC	26-12-16-13
eClass 5.1	27-06-91-90	eClass 6.2	27-27-92-18
eClass 7.1	27-06-91-90		

Approvals

Approvals



ROHS


Conform

SAIL-M8BG-4-5.0V


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen


Dimensioned drawing



Pole scheme



Circuit diagram



The ideal tool, the Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F