

**SAI Active
SAI-AU M12 SB 4Thermo****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Besides the well-known digital input and output modules, the SAI-Pro-System also includes meter components, thermo, PT100 and analogue modules. Its comprehensive range offers users a wide choice.

General ordering data

Type	SAI-AU M12 SB 4Thermo
Order No.	1938720000
Version	SAI Active, Subbus
GTIN (EAN)	4032248612703
Qty.	1 pc(s).

SAI Active SAI-AU M12 SB 4Thermo

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	155 mm	Width	30 mm
Height	32 mm	Net weight	282 g

Configuration

System integration	automatic
--------------------	-----------

Connections

Connection to Subbus (SUB-IN)	1 x M8 plug 4-pole, A-coded	Connection to Subbus (SUB-OUT)	1 x M8 female 4-pole, A-coded
I/O connections	4 x M12 female, 5-pole A-coded		

Digital inputs

Input filter	configurable
--------------	--------------

General data

Certificate	CE, cULus	Earth	< 200 g
Housing main material	Pocan, PBT	L x W x H	155 / 30 / 32
Protection degree	IP 67	UL 94 flammability rating	5VA

Fieldbus

Addressing	automatic	Bus system	Subbus
------------	-----------	------------	--------

Functional inputs

Conversion time	250 ms (can be configured to 70 ms)	Input filter	configurable
Measurement error	< ± 0.5% (of measuring range limit)	Resolution	0.1 °C per digit
Sensor	Types J, K, L, B, E, N, R, S, T, U: mV readings	Temperature range	Typical for sensor, Preset Type K, -100 °C to 1370 °C
cold junction compensation	External PT1000 connection on pins 1 and 3 (GND)		

Supply voltage

Limits	18 V DC ... 30 V DC	Operating voltage	24 V
Reverse polarity protection	Yes		

Classifications

ETIM 3.0	EC001597	UNSPSC	43-17-27-10
eClass 5.1	27-25-04-03	eClass 6.2	27-24-26-04
eClass 7.1	27-24-26-04		

SAI Active **SAI-AU M12 SB 4Thermo**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform