

FP Box 10P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FieldPower® power distributors support error-free installation in an extremely short space of time. Branches and functions integrated in the cover can simply be plugged in. Robust with high protection degree. For cable seals consult accessories

General ordering data

Type	FP Box 10P
Order No.	1957590000
Version	FieldPower® Box, IP65, Polycarbonate, GF 10, AC Box
GTIN (EAN)	4032248636662
Qty.	1 pc(s).

FP Box 10P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	181 mm	Length (inches)	7.126 inch
Width	192 mm	Width (inches)	7.559 inch
Height	67 mm	Height (inches)	2.638 inch
Net weight	950 g		

Temperatures

Operating temperature, max.	55 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...55 °C	Storage temperature	-40 °C...85 °C
Temperature range, installation, min.	10 °C	Temperature range, installation, max.	40 °C

Approvals

Institute (UL)



Certificate No. (UL)

E310075

Clamping capacity, Push-In connection, distribution

Blade size	0.6 x 3.5 mm	Blade size, PUSH IN connection	0.6 x 3.5 mm
Cross-section for connected wire PUSH IN connection, solid, min.	0.5 mm ²	Cross-section for connected wire, PUSH IN connection, solid, max.	6 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible, PUSH IN connection, max.	10 mm ²	Cross-section for connected wire, flexible, PUSH IN connection, min.	0.5 mm ²
Finely-stranded flexible, max. PUSH IN connection	6 mm ²	Finely-stranded flexible, min. PUSH IN connection	0.5 mm ²
Stripping length, PUSH IN connection	14 mm	Wire connection cross section, stranded, PUSH IN connection, max.	6 mm ²
Wire connection cross section, stranded, PUSH IN connection, min.	0.5 mm ²		

FP Box 10P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

IDC connection clamping capacity, power cable

Blade size	0.6 x 3.5 mm	Connection cross-section, finely stranded, max.	6 mm ²
Connection cross-section, finely stranded, min.	2.5 mm ²	Connection cross-section, stranded, max.	6 mm ²
Connection cross-section, stranded, min.	2.5 mm ²	Wire connection cross section, finely stranded, max.	6 mm ²
Wire connection cross-section, finely stranded, min.	2.5 mm ²	Wire cross-section, solid, max.	6 mm ²
Wire cross-section, solid, min.	1.5 mm ²		

General information #96 connectors

Can be coded	Yes, Coded on PE	UL 94 flammability rating	5VA
--------------	------------------	---------------------------	-----

General data

Can be coded	Yes, Coded on PE	Connection 2	PTDS4 plug, PTS4 plug
Material colour	black	Protection degree	IP65
Silicone	No	Insulating material	Polycarbonate, GF 10
Halogen	No	UL 94 flammability rating	5VA

Dimensions of box

Height	67 mm	Length	181 mm
Width	192 mm		

Rated data acc. to IEC

Rated cross-section	6 mm ²	Rated current	41 A
Rated impulse withstand voltage	8 kV	Rated voltage	800 V
Standards	UL 2237, IEC 60947-7-1		

Rated data acc. to UL

Rated current (Use group D / UL 1059)	30 A	Rated voltage (Use group D / UL 1059)	600 V
Standards	UL 2237, IEC 60947-7-1	Wire connection cross section AWG, max.	AWG 10
Wire connection cross section AWG, min.	AWG 14		

Classifications

ETIM 3.0	EC000214	ETIM 4.0	EC000214
ETIM 5.0	EC000214	ETIM 6.0	EC000214
UNSPSC	43-17-27-02	eClass 5.1	27-14-24-04
eClass 6.2	27-14-24-09	eClass 7.1	27-14-24-09
eClass 8.1	27-14-24-09	eClass 9.0	27-14-24-09
eClass 9.1	27-14-24-09		

Data sheet**FP Box 10P**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

DownloadsApproval/Certificate/Document of
Conformity[Herstellererklärung_DE](#)
[FieldPower](#)

Engineering Data

[WSCAD](#)