

**RSSD
RS SD37 SZ**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Similar to illustration

Passive interfaces for signal transmission on a SubD connector equipped with a tension-clamp connection in accordance with IEC 807-2 / DIN 41652. The main features include:

- Group with 9-, 15-, 37- and 50-pole male and female connectors.
- One-to-one electrical connection between controller and field connections.
- Extremely compact modules for attachment to standard TS35 or TS32 rail.

General ordering data

| | |
|------------|--|
| Type | RS SD37 SZ |
| Order No. | 8537240000 |
| Version | Interface, RSSD, D-sub connectors, acc. to IEC 60807 / DIN 41652, 37-pole plug, Tension-clamp connection |
| GTIN (EAN) | 4032248172993 |
| Qty. | 1 pc(s). |

**RSSD
RS SD37 SZ**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Length | 110 mm | Length (inches) | 4.331 inch |
| Width | 87 mm | Width (inches) | 3.425 inch |
| Height | 63.6 mm | Height (inches) | 2.504 inch |
| Net weight | 153.28 g | | |

Temperatures

| | | | |
|-----------------------------|-----------|-----------------------------|-------------|
| Operating temperature, max. | 55 °C | Operating temperature, min. | 0 °C |
| Storage temperature, max. | 70 °C | Storage temperature, min. | -40 °C |
| Operating temperature | 0...55 °C | Storage temperature | -40...70 °C |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Connection Data

| | | | |
|----------------------------|---|--------------------------------|---------------|
| Connection on control side | D-sub connectors, acc. to IEC 60807 / DIN 41652 | Number of poles (control side) | 37-pole plug |
| Design of locking system | UNC 4/40 | Connection (field side) | LM2NZF 5.08mm |
| Earthing | No | | |

Rating data

| | | | |
|---------------|-------|------------------------------|-------|
| Rated voltage | 100 V | Rated current per connection | 1.5 A |
|---------------|-------|------------------------------|-------|

Insulation coordination (EN50178)

| | | | |
|-------------------------------|--------------|--------------------------|-------|
| According to | DIN EN 50178 | Rated insulation voltage | 100 V |
| Surge voltage category | II | Pollution severity level | 2 |
| Pulse voltage test (1,2/50µs) | 0.8 kV | | |

Connection field

| | | | |
|------------------------------|--------------------------|----------------------------------|----------------------|
| Type of connection | Tension-clamp connection | Clamping range, min. | 0.13 mm ² |
| Clamping range, max. | 2.5 mm ² | Solid, min. H05(07) V-U | 0.2 mm ² |
| Solid, max. H05(07) V-U | 2.5 mm ² | Flexible, min. H05(07) V-K | 0.2 mm ² |
| Flexible, max. H05(07) V-K | 1.5 mm ² | Flexible with sleeve, max. | 1.5 mm ² |
| Flexible with sleeve, min. | 0.25 mm ² | Sleeve with plastic collar, max. | 1.5 mm ² |
| Min. wire cross-section, AWG | AWG 24 | Max. wire cross-section, AWG | AWG 14 |
| Stripping length | 7.5 mm | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001419 | ETIM 4.0 | EC001421 |
| ETIM 5.0 | EC001421 | ETIM 6.0 | EC002780 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-24-22-04 |
| eClass 6.2 | 27-24-22-04 | eClass 7.1 | 27-14-11-52 |
| eClass 8.1 | 27-14-11-52 | eClass 9.0 | 27-14-11-52 |
| eClass 9.1 | 27-14-11-52 | | |

Data sheet

**RSSD
RS SD37 SZ**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data

[WSCAD](#)

Data sheet

**RSSD
RS SD37 SZ**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



N: Number of poles