

**WAVESERIES
WAVEFILTER 6A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Simple radio noise suppression in the cabinet
thanks to WAVEFILTER**

The WAVEFILTER series eliminates the need for time-consuming bolting processes of mains filters. The filters are snapped onto TS 35 and connected to the device whose noise is to be suppressed. The two-stage, 22.5 mm wide WAVEFILTER, in 1 A, 3 A, 6 A and 10 A versions, offers high attenuation at all voltage levels from 5 V, 12 V, 24 V, 48 V, 60 V, 120 V up to 250 V.

General ordering data

Available until	2019-03-31
Type	WAVEFILTER 6A
Order No.	8614800000
Version	WAVESERIES, Surge protection, Surge protection, Attenuation at 100 MHz: 40 dB
GTIN (EAN)	4032248277094
Qty.	1 pc(s).

WAVESERIES WAVEFILTER 6A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	22.5 mm	Width (inches)	0.886 inch
Height	73.4 mm	Height (inches)	2.89 inch
Depth	73.4 mm	Depth (inches)	2.89 inch
Net weight	112.12 g		

Temperatures

Operating temperature, max.	40 °C	Operating temperature, min.	-20 °C
Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Operating temperature	-20 °C...40 °C	Storage temperature	-25 °C...55 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Certificate No. (cURus)	E64388
-------------------------	--------

General data

Colour	beige	Design	Wave 22.5 L
Height with TS 35	112.4 mm	Protection degree	IP20
Rail	TS 35	Segment	Power distribution
Version	Surge protection		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Rated data IEC / EN

Attenuation at 0.15 MHz	< 0.5 dB	Attenuation at 1 MHz	18 dB
Attenuation at 10 MHz	45 dB	Attenuation at 100 MHz	40 dB
Capacitance	C _x : 33 nF / C _{and} : 22 nF	Fuse	6.3 A
Inductance L and L1	0.8 mH	Leakage current at U _n	190 µA
Rated current I _N	6 A	Rated voltage (AC)	250 V
Rated voltage (DC)	250 V	Test voltage P-N	1700 V DC
Test voltage P/N-PE	2000 V AC	Voltage type	AC/DC

Connection data

Cross-section	2.5 mm ²	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire connection cross-section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	2.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	1.5 mm ²

**WAVESERIES
WAVEFILTER 6A**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Classifications**

ETIM 3.0	EC000943	ETIM 4.0	EC000943
ETIM 5.0	EC000943	ETIM 6.0	EC002623
UNSPSC	30-21-18-01	eClass 5.1	27-26-03-01
eClass 6.2	27-26-03-90	eClass 7.1	27-26-03-90
eClass 8.1	27-26-03-90	eClass 9.0	27-18-28-14
eClass 9.1	27-42-02-08		

Approvals

Approvals



ROHS

Conform

Downloads


Approval/Certificate/Document of Conformity	Declaration of Conformity Declaration of Conformity
Brochure/Catalogue	CAT 4.4 ELECTR 16/17 EN
Engineering Data	EPLAN, WSCAD
User Documentation	Operating instructions

WAVESERIES WAVEFILTER 6A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol



Circuit diagram

