

## INSTA CP SNT 25W 5V 5A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



One-phase switched-mode power unit in installation housing in performance classes 24 and 48 W. .  
The INSTA power units can be universally deployed because of their wide input range from 85 V AC to 265 V AC.  
They are available with output voltages from 5 V to 48 V.

### General ordering data

Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2020-03-31
Type	CP SNT 25W 5V 5A
Order No.	<a href="#">8754960000</a>
Version	Power supply, switch-mode power supply unit, 5 V
GTIN (EAN)	4032248426119
Qty.	1 pc(s).
Alternative product	<a href="#">2580210000</a>

**INSTA  
CP SNT 25W 5V 5A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	70 mm	Width (inches)	2.756 inch
Height	90.5 mm	Height (inches)	3.563 inch
Depth	62.5 mm	Depth (inches)	2.461 inch
Weight	0.2 kg	Net weight	346 g

**Temperatures**

Humidity at operating temperature	5...95% (indoor), T <sub>u</sub> = 40°C, without condensation	Operating temperature, max.	70 °C (Derating ab 55 °C)
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-20 °C	Operating temperature	-10 °C...70 °C (Derating ab 55 °C)
Storage temperature	-20 °C...85 °C		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Rated data UL**

Certificate No. (cURus)	E255651	Certificate No. (UL)	E258476
-------------------------	---------	----------------------	---------

**Input**

Connection system	Screw connection	DC input voltage range	80...370 V DC
Input current	500 mA at rated load @ 230 V AC	Input current at 115 Vac	500 mA
Input current at 230 Vac	500 mA	Input frequency	50/ 60 Hz
Input fuse	Fusible link 2.5 A (T) / 250 V	Input voltage (voltage mode input)	85...264 V AC / 110...370 V DC
Inrush Current Limitation	Yes	Wire connection method	Screw connection

**output**

Control at 10...100% load	1%	Mains failure bridge-over time	11 ms @ 115 V AC / 50 ms @ 230 V AC
Max. capacitance at output	10000 µF	Max. residual ripple	120 mV <sub>ss</sub>
Output current	5 A	Output power	25 W
Output voltage	5 V	Output voltage	4...8 V (adjustable via potentiometer)
Output voltage type	DC	Overload protection	105 %...150 % I <sub>konst</sub> of max. Output line; automatic reboot
Parallel connection option	Max. 3 devices (rated voltages are to be calibrated at ±20 mV)	Surge protection	Varistor
Wire connection method	Screw connection		

**Data sheet**

**INSTA  
CP SNT 25W 5V 5A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**General data**

Building Width	62.5 mm	Building height	90.5 mm
Degree of efficiency at max. load	70%	EMC standards	EN 55011, EN 55022, EN 61000-3-2,-3, EN 61000-6-2,-3,-4
Installation advice	For side-by-side mounting, clearance: above/below > 30 mm	MTBF	> 500,000 h in accordance with IEC 61709 (SN29500)
Mounting position, installation notice	horizontally, on terminal rail TS 35	Operating temperature	-10 °C...70 °C (Derating ab 55 °C)
Protection degree	IP20	Short-circuit protection	Yes
Standards	DIN EN 50178 (PELV), DIN EN 60950 (SELV)	Status indication	Green LED
Weight	0.2 kg		

**System data**

Output current	5 A
----------------	-----

**Insulation coordination**

Humidity at operating temperature	5...95% (indoor), T <sub>u</sub> = 40°C, without condensation	electrical isolation, I/O rail	4 kV
electrical isolation, input-earth	1.5 kV	electrical isolation, input-output	3 kV
electrical isolation, output-earth	0.5 kV		



**Connection data (input)**

Connection system	Screw connection
-------------------	------------------

**Signalling**

Status indication	Green LED
-------------------	-----------

**Approvals**

Institute (UL)		Certificate No. (UL)	E258476
Institute (cURus)		Certificate No. (cURus)	E255651

**Classifications**

ETIM 3.0	EC001039	ETIM 4.0	EC002541
ETIM 5.0	EC002541	ETIM 6.0	EC002540
UNSPSC	30-21-18-01	eClass 5.1	27-04-90-02
eClass 6.2	27-04-90-04	eClass 7.1	27-04-90-04
eClass 8.1	27-04-90-04	eClass 9.0	27-04-07-01
eClass 9.1	27-04-07-01		

**Data sheet****INSTA  
CP SNT 25W 5V 5A****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DE_PA5200_160310_003.pdf</a>
Brochure/Catalogue	<a href="#">CAT 4.3 ELECTR 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">Warrenty_Information_Power_Supplies.pdf</a> <a href="#">Operating Instructions</a>

**Data sheet**

**INSTA  
CP SNT 25W 5V 5A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

**Electric symbol**

