

**Industrial Ethernet  
IE-FM5D2UE0001MSD0SD0X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 50 µm

**General ordering data**

Type	IE-FM5D2UE0001MSD0SD0X
Order No.	<a href="#">8876430010</a>
Version	Dragline cable, SC duplex IP 20, SC duplex IP 20, 50 µm, PUR, 1 m
GTIN (EAN)	4032248609864
Qty.	1 pc(s).

**Industrial Ethernet  
IE-FM5D2UE0001MSD0SD0X**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	1 m	Length (inches)	0.039 inch
Net weight	70 g		

**Temperatures**

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...80 °C	Storage temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

**Standards**

Connector standard	IEC 61754-4
--------------------	-------------

**Fibre-optic**

Attenuation	2.3 dB/km at 850 nm, &le; 0.5 dB/km at 1300 nm	Bandwidth	500 MHz*km at 850 nm, 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM2	Insertion loss	≤ 0.4 dB
Return loss (attenuation)	≥ 30 dB		

**Cable structure**

Core diameter	50 µm	Sheath diameter	6 mm
Cable layout	Break-out dragline	Material sheath	PUR
Sheathing colour	black		

**Mechanical and material properties of cable**

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	77 mm		

**plug**

Connector left	SC duplex IP 20	Connector right	SC duplex IP 20
----------------	-----------------	-----------------	-----------------

**Classifications**

ETIM 3.0	EC000034	ETIM 4.0	EC000034
ETIM 5.0	EC000034	ETIM 6.0	EC002607
UNSPSC	30-21-18-01	eClass 5.1	27-06-18-03
eClass 6.2	27-06-18-03	eClass 7.1	27-06-18-03
eClass 8.1	27-06-18-03	eClass 9.0	27-06-10-03
eClass 9.1	27-06-10-03		

**Approvals**

ROHS	Conform
------	---------

**Industrial Ethernet  
IE-FM5D2UE0001MSD0SD0X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Downloads**

---

Brochure/Catalogue	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>

---

**Data sheet**

**Industrial Ethernet  
IE-FM5D2UE0001MSD0SD0X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Detailed drawing**

---

---

