

**Cutting tools
KT 80**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Type	KT 80
Order No.	9202080000
Version	Cutting tools ,Circular cable cutter
GTIN (EAN)	4032248482313
Qty.	1 pc(s).

**Cutting tools
KT 80**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	675 mm	Width (inches)	26.575 inch
Height	175 mm	Height (inches)	6.89 inch
Depth	55 mm	Depth (inches)	2.165 inch
Weight	3,240 g	Net weight	3,500 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	One-hand mechanical
---------	---------------------

Cutting tools

Aluminium sector cable	4 x 240 SE	Copper cable - flexible, max.	630 mm ²
Copper cable - flexible, max. (kcmil)	1,260 kcmil	Copper cable - stranded, max.	630 mm ²
Copper cable - stranded, max. (kcmil)	1,260 kcmil	Copper cable, max. diameter	80 mm
Copper sector cable	3 x 240 SM	Data / telephone / control cable, max. Ø	80 mm
Stranded aluminium cable, max (mm ²)	1,000 mm ²	Stranded aluminium cable, max. (kcmil)	2,000 kcmil

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000142	ETIM 6.0	EC000142
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	21-04-38-90	eClass 7.1	21-04-90-11
eClass 8.1	21-04-90-11	eClass 9.0	21-04-47-01
eClass 9.1	21-04-90-11		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

Data sheet**Cutting tools
KT 80**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Example of use**

-  Cu + Al: max. 80 mm
-  Cu: max. 630 mm²
Al: max. 1000 mm²
-  Cu: max. 630 mm²

