

Testing tools
MULTIMETER C 2606

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Digital current clamp devices and attachments and adapters are used for measuring AC and DC currents. The significant advantage of these devices is that you can make a measurement without breaking the flow of current.

General ordering data

Type	MULTIMETER C 2606
Order No.	9427370000
Version	Digital clamp-on measuring device
GTIN (EAN)	4032248407019
Qty.	1 pc(s).

**Testing tools
MULTIMETER C 2606**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	277 mm	Width (inches)	10.905 inch
Height	49 mm	Height (inches)	1.929 inch
Depth	102 mm	Depth (inches)	4.016 inch
Weight	540 g	Net weight	888.2 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Measuring and testing devices

AC voltage measuring range	0.4 - 1,000 V	Battery type	9V block battery
DC voltage measuring range	0.4 - 1000 V	Display	digital
Frequency measurement	Yes	Frequency range, max.	400 kHz
Frequency range, min.	0.1 kHz	Measured capacitance value, max.	4 µF
Measured capacitance value, min.	40 nF	Measured current value, max.	1,000 A
Measuring range category	CAT III	Opening width of current-measuring clamp-on attachment	57 mm
Resistance measuring range, max.	40 MΩ	Resistance measuring range, min.	0.4 Ω
Resolution of AC voltage	± 0.5%	Resolution of DC voltage	± 0.5%
Selection of measuring range	Manual	Tested and approved according to	VDE 0680, Part 5
Type of current	AC, DC	Working temperature, max.	50 °C
Working temperature, min.	0 °C		

Classifications

ETIM 3.0	EC000380	ETIM 4.0	EC000380
ETIM 5.0	EC000380	ETIM 6.0	EC000380
UNSPSC	41-11-36-37	eClass 5.1	27-20-03-12
eClass 6.2	27-20-03-12	eClass 7.1	27-20-03-12
eClass 8.1	27-20-03-12	eClass 9.0	27-20-03-12
eClass 9.1	27-20-03-12		

Product information

Product information Min/max function only applies for the DC range.

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

Data sheet

Testing tools
MULTIMETER C 2606

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

