Industrial Ethernet
IE-C6ES8UG0120A45A40-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.
The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5 , 6 and 14
- Cat. 6 throughout$_A$ with ***STEADY****TEC*® technolgy
- pre-assembled cables and cables sold by the metre
- Copper and fibre-optic cables
- in IP20 and IP67
- all relevant industrial connections: RJ45, M12, SC, ...
- comprehensive range of accessories

General ordering data

Available until	2012-12-31
Type	IE-C6ES8UG0120A45A40-X
Order No.	8950550120
Version	System cable, RJ45 IP 67 RockStar V05 metal, RJ45 IP 20, Cat.6$_A$ / Class E$_A$ (ISO/IEC 11801 2010), PUR, 12 m
GTIN (EAN)	4032248741519
Qty.	1 pc(s).

Industrial Ethernet
IE-C6ES8UG0120A45A40-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	12 m	Length (inches)	0.472 inch
Net weight	657 g	Insulation cross-section	1.03 mm

Temperatures

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...80 °C	Storage temperature	-40 °C...80 °C
Installation temperature	-15 °C...60 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
Connector standard	IEC 61076-3-106 Var. 5, IEC 60603-7-51	Standard, assembly	UL-Style 20963 (80°C/30V)

Cable structure

Wire material	Stranded tin-plated copper wire	Standard designations	S/FTP, LIO2YSC11Y 4x2x0.15 PIMF FRNC GN
Strands	7	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm²
Insulation	PE	Insulation cross-section	1.03 mm
Arrangement of wire cores	Twisted pair	Wire pair shielding	Aluminium foil
Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown	Shielding	S/FTP
Complete shielding	Shielding braid made from copper wiring	Shielding braid thickness	0.1 mm
Material sheath	PUR	Sheath diameter, min.	6.2 mm
Sheath diameter, max.	6.6 mm	Sheathing colour	green (RAL 6018)

Electrical properties of cable

Category	Cat.6_A / Class E_A (ISO/IEC 11801 2010)	Test voltage: wire-wire-shield	700 V AC
Characteristic impedance	100 ± 5 Ω at 100MHz	Loop resistance	290 Ω/km
Deviation	3 ns/100m	Transfer impedance	15 mΩ/m at 1 MHz, 10 mΩ/m at 10 MHz, 30 mΩ/m at 30 MHz
Capacity at 1 kHz	45 nF/km	Signal propagation time	4.5 ns/m

Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
Pulling force	≤ 100 N	Abrasion resistance	very good
Resistance to spread of flame	in accordance with IEC 60332-1	Resistance to oils	in accordance with IEC 60811-2-1
Halogen	halogen-free, according to IEC 60754-2	Corrosiveness of fumes	to IEC 60754-2

Industrial Ethernet
IE-C6ES8UG0120A45A40-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

plug

Connector left	RJ45 IP 67 RockStar V05 metal	Connector right	RJ45 IP 20

Classifications

ETIM 3.0	EC001262	ETIM 4.0	EC000830
ETIM 5.0	EC000830	ETIM 6.0	EC002599
UNSPSC	26-12-16-06	eClass 5.1	27-06-18-02
eClass 6.2	27-06-18-01	eClass 7.1	27-06-18-01
eClass 8.1	27-06-18-01	eClass 9.0	27-06-03-08
eClass 9.1	27-06-03-08		

Approvals

ROHS	Conform

Downloads

Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN