

**Cutting tools
KTF 36**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- Suitable in situations where cables have to be cut in confined spaces
- Easy handling
- Minimal manual force required
- Release option in every cutting position
- Not suitable for steel wires, steel-armoured cables, aluminium alloys and hard-drawn copper conductors
- Do not cut live conductors

General ordering data

Type	KTF 36
Order No.	9002190000
Version	Cutting tools ,Front cutter ,35mm ,Copper and aluminium
GTIN (EAN)	4008190066345
Qty.	1 pc(s).

Data sheet

**Cutting tools
KTF 36**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	360 mm	Width (inches)	14.173 inch
Height	150 mm	Height (inches)	5.905 inch
Depth	50 mm	Depth (inches)	1.969 inch
Weight	1,918 g	Net weight	1,642.78 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Technical data

Version One-hand mechanical

Cutting tools

Cable type	Copper and aluminium cables	Copper cable - flexible, max.	300 mm ²
Copper cable - flexible, max. (kcmil)	600 kcmil	Copper cable - stranded, max.	300 mm ²
Copper cable - stranded, max. (kcmil)	600 kcmil	Copper cable, max. diameter	35 mm
Max. conductor diameter	36 mm	Stranded aluminium cable, max (mm ²)	300 mm ²
Stranded aluminium cable, max. (kcmil)	600 kcmil	Stranded aluminium cable, max. diameter	35 mm

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000142	ETIM 6.0	EC000142
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	21-04-90-90	eClass 7.1	21-04-90-11
eClass 8.1	21-04-90-11	eClass 9.0	21-04-47-01
eClass 9.1	21-04-90-11		

Approvals

Approvals



Downloads




Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

Data sheet

Cutting tools
KTF 36

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

-
-  Cu + Al: max. 35 mm
 -  Cu: max. 300 mm²
Al: max. 300 mm²
 -  Cu: max. 300 mm²
-
-
-