

TBF (polyester empty enclosure) TBF 56/30/18 7035

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Polyester housings The housings of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

Features:

- 9 sizes in 2 versions
- cover with nylon screws
- fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories Weidmüller can manufacture and supply this housing to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Type	TBF 56/30/18 7035
Order No.	9502810000
GTIN (EAN)	4032248235209
Qty.	1 pc(s).

TBF (polyester empty enclosure) TBF 56/30/18 7035

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	302 mm	Width (inches)	11.89 inch
Height	558 mm	Height (inches)	21.968 inch
Depth	175 mm	Depth (inches)	6.89 inch
Weight	3,970 g	Net weight	4,420 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Cable glands, right

M12	80	M16	46
M20	40	M25	18
M32	8	M40	6
M50	4	M63	4

Cable glands, top/bottom

M12	44	M16	24
M20	20	M25	10
M32	4	M40	3
M50	3	M63	2

General information

Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction	Standards	IEC 61439-2, IEC 60529, EN 61439-2, EN 60529, EN 62208
Toxicity	Free from halogens	UL 94 flammability rating	HB
Material	Glass fibre-reinforced polyester	Seal material	Polyurethane
Operating temperature, min.	-50 °C	Operating temperature, max.	130 °C
Impact resistance	IK08 in accordance with IEC 62208, IK10 in accordance with IEC 62262	Protection degree	IP67
Enclosure attachment	6.5 mm hole in enclosure base	Lid attachment	Crosshead nylon screws
Integral fixing	4 or 6 stud bolts M6 inner (female) thread		

General information on accessories

Material Glass fibre-reinforced polyester

horizontal assembly

WDU 10 / ZDU 10	4x22	WDU 16 / ZDU 16	4x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	4x44	WDU 35 / ZDU 35	4x14
WDU 4 / ZDU 4	4x37	WDU 6 / ZDU 6	4x28

Data sheet

**TBF (polyester empty enclosure)
TBF 56/30/18 7035**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

vertical assembly

WDU 10 / ZDU 10	2x48	WDU 16 / ZDU 16	2x34
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x94	WDU 35 / ZDU 35	2x30
WDU 4 / ZDU 4	2x79	WDU 6 / ZDU 6	2x59

Classifications

ETIM 3.0	EC000058	ETIM 4.0	EC000058
ETIM 5.0	EC000058	ETIM 6.0	EC000261
UNSPSC	31-26-15-02	eClass 5.1	27-14-91-07
eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
eClass 8.1	27-14-91-07	eClass 9.0	27-18-01-01
eClass 9.1	27-18-92-90		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN_WSCAD
Engineering Data	STEP

Data sheet**TBF (polyester empty enclosure)
TBF 56/30/18 7035****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Drawings**