

**SAK Series
EK 2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



In order to do justice to the different requirements placed on our products, it is necessary to use various insulating materials tailored to the particular application. None of the insulating materials used by Weidmüller contain any hazardous substances. Above all, we ensure that all our materials are free from cadmium. Furthermore, they contain no colour pigments based on heavy metals and do not lead to the formation of dioxin/furan.

General ordering data

Type	EK 2
Order No.	0323100000
Version	SAK Series, PE terminal, Rated cross-section: 10 mm², Screw connection
GTIN (EAN)	4008190013585
Qty.	20 pc(s).

SAK Series EK 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	52 mm	Width	10.2 mm
Height	38 mm	Height of lowest version	38 mm
Weight	32.55 g	Net weight	32.9 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Number of similar terminals	1
Open sides	closed	Type of mounting	Screwed
Version	Screw connection, With PE connection		

CSA ratings data

Certificate No. (CSA)	12400-236	Wire cross section max. (CSA)	8 AWG
Wire cross section min. (CSA)	26 AWG		

Clampable wires (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min.	1.5 mm ²	Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.	10 mm ²
---	---------------------	---	--------------------

Clampable wires (rated connection)

Type of connection	Screw connection	Stripping length	14 mm
Blade size	1.0 x 5.5 mm	Connection direction	on side
Number of connections	2	Clamping range, rated connection, min.	1.5 mm ²
Clamping range, rated connection, max.	10 mm ²	Clamping screw	M 4
Tightening torque, min.	1.2 Nm	Tightening torque, max.	1.6 Nm
Torque level with DMS electric screwdriver	4	Gauge to IEC 60947-1	B6
Wire connection cross section, solid core, max. rated connection	1.5 mm ²	Wire connection cross section, solid core max. rated connection	10 mm ²
Wire connection cross section, stranded, rated connection, min.	1.5 mm ²	Wire connection cross section, stranded, rated connection, max.	10 mm ²
Wire connection cross section, finely stranded, max.	10 mm ²	Wire connection cross-section, finely stranded, min.	1.5 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	1.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	10 mm ²
Wire connection cross section AWG, min.	AWG 16	Wire connection cross section AWG, max.	AWG 8

Rated data

Rated cross-section	10 mm ²	Standards	IEC 60947-7-2
---------------------	--------------------	-----------	---------------

Material data

Colour	Yellow, Green
--------	---------------

SAK Series EK 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

System specifications

Product family	SAK Series	Type of connection	Screw connection
Connection direction	on side	Number of levels	1
Number of connections	2	No. of clamping points per level	2
Levels cross-connected internally	No	Mounting rail	TS 32
End cover plate required	No		

Classifications

ETIM 3.0	EC000901	UNSPSC	30-21-18-11
eClass 5.1	27-14-03-05	eClass 6.2	27-14-03-05
eClass 7.1	27-14-03-05		

Approvals

Approvals



ROHS

Conform