

**H16,0/12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

**General ordering data**

|            |                                      |
|------------|--------------------------------------|
| Type       | H16,0/12                             |
| Order No.  | <a href="#">0492500000</a>           |
| Version    | Wire end ferrule, 16 mm <sup>2</sup> |
| GTIN (EAN) | 4008190114190                        |
| Qty.       | 500 pc(s).                           |

**Datenblatt**

**H16,0/12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

|        |       |            |        |
|--------|-------|------------|--------|
| Length | 12 mm | Net weight | 0.35 g |
|--------|-------|------------|--------|

**Product data**

|                               |                    |   |        |
|-------------------------------|--------------------|---|--------|
| Conductor cross-section       | 16 mm <sup>2</sup> | Wire connection cross section AWG, max. | AWG 6  |
| Contact surface diameter (D1) | 5.8 mm             | Collar diameter (D2)                    | 7.5 mm |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000005    | UNSPSC     | 31-16-31-02 |
| eClass 5.1 | 27-40-02-01 | eClass 6.2 | 27-40-02-01 |
| eClass 7.1 | 27-40-02-01 |            |             |

**Approvals**

Approvals



ROHS Conform