

**SAK Series  
QL 2 SAKG28**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                                                                         |
|------------|-------------------------------------------------------------------------|
| Type       | QL 2 SAKG28                                                             |
| Order No.  | <a href="#">0551200000</a>                                              |
| Version    | SAK Series, Cross-connector, for cross-connection link, No. of poles: 2 |
| GTIN (EAN) | 4008190038526                                                           |
| Qty.       | 10 pc(s).                                                               |

**SAK Series**  
**QL 2 SAKG28**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 40 mm   | Width (inches)  | 1.575 inch |
| Height     | 14 mm   | Height (inches) | 0.551 inch |
| Depth      | 4 mm    | Depth (inches)  | 0.157 inch |
| Net weight | 16.95 g |                 |            |

**Temperatures**

|                           |               |                           |       |
|---------------------------|---------------|---------------------------|-------|
| Storage temperature, max. | 40 °C         | Storage temperature, min. | 10 °C |
| Storage temperature       | 10 °C...40 °C |                           |       |

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Material data**

|          |      |        |      |
|----------|------|--------|------|
| Material | CuSn | Colour | grey |
|----------|------|--------|------|

**System specifications**

|         |                           |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

**Additional technical data**

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in |                     |                 |

**Dimensions**

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 28 mm |
|-----------------|-------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | ETIM 4.0   | EC000489    |
| ETIM 5.0   | EC000489    | ETIM 6.0   | EC000489    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 27-14-11-40 |
| eClass 6.2 | 27-14-11-40 | eClass 7.1 | 27-14-11-40 |
| eClass 8.1 | 27-14-11-40 | eClass 9.0 | 27-14-11-40 |
| eClass 9.1 | 27-14-11-40 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                       |
|------------------|-----------------------|
| Engineering Data | <a href="#">WSCAD</a> |
|------------------|-----------------------|