

**TBF (polyester empty enclosure)  
MP TBF 19/15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



**Polyester housings** The housings of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

**Features:**

- 9 sizes in 2 versions
- cover with nylon screws
- fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories Weidmüller can manufacture and supply this housing to match customer specifications, fitted with all necessary terminals and cable glands.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | MP TBF 19/15               |
| Order No.  | <a href="#">9502720000</a> |
| GTIN (EAN) | 4032248002139              |
| Qty.       | 1 pc(s).                   |

**TBF (polyester empty enclosure)  
MP TBF 19/15**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 99 mm  | Width (inches)  | 3.898 inch |
| Height     | 134 mm | Height (inches) | 5.276 inch |
| Depth      | 2 mm   | Depth (inches)  | 0.079 inch |
| Net weight | 205 g  |                 |            |

**General information**

|                    |      |          |                         |
|--------------------|------|----------|-------------------------|
| Material thickness | 2 mm | Material | Sheet steel, galvanized |
|--------------------|------|----------|-------------------------|

**General information on accessories**

|                |                         |                    |      |
|----------------|-------------------------|--------------------|------|
| Material       | Sheet steel, galvanized | Material thickness | 2 mm |
| Type of fixing | when screwed in         |                    |      |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000318    | ETIM 4.0   | EC002620    |
| ETIM 5.0   | EC002620    | ETIM 6.0   | EC000213    |
| UNSPSC     | 31-16-23-03 | eClass 5.1 | 27-18-92-07 |
| eClass 6.2 | 27-18-92-61 | eClass 7.1 | 27-18-92-61 |
| eClass 8.1 | 27-18-92-61 | eClass 9.0 | 27-40-06-39 |
| eClass 9.1 | 27-18-92-90 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                     |
|--------------------|-------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 5 ENCL 17/18 EN</a> |
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>        |