

SAK Series
AP AST1+5 DB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

| | |
|------------|--|
| Type | AP AST1+5 DB |
| Order No. | 0266400000 |
| Version | SAK Series, End plate, 1.5 mm, dark beige, Direct mounting |
| GTIN (EAN) | 4008190176488 |
| Qty. | 20 pc(s). |

**SAK Series
AP AST1+5 DB**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Width | 1.5 mm | Width (inches) | 0.059 inch |
| Height | 58 mm | Height (inches) | 2.283 inch |
| Depth | 30 mm | Depth (inches) | 1.181 inch |
| Net weight | 3.2 g | | |

Temperatures

| | | | |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max. | 40 °C | Storage temperature, min. | 10 °C |
| Storage temperature | 10 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | | | |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000886 | ETIM 4.0 | EC000886 |
| ETIM 5.0 | EC000886 | ETIM 6.0 | EC000886 |
| UNSPSC | 30-21-18-27 | eClass 5.1 | 27-14-11-33 |
| eClass 6.2 | 27-14-11-33 | eClass 7.1 | 27-14-11-33 |
| eClass 8.1 | 27-14-11-33 | eClass 9.1 | 27-14-11-33 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------|
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |