

Cable glands KDSU M32 BS O SC 1 G32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The KDSU features a special ring in the shape of a truncated cone. The ring enables connections between single-wire-armoured and metal-foil-armoured cables and braided-armoured lines. This ensures a conductive connection between the cable and the cable gland. It is also possible to connect non-armoured cables and lines. In addition, the KDSU comes with two separate seals which provide sealing for the outer and inner parts of the cable insulation. The cable armouring is located between the inner and outer insulation. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -20°C to +85°C. When using a silicone seal, a temperature range of -60°C to +180°C is possible. The O-ring and the cable gland included in the delivery are made from the same material. When using both sealing materials, IP66 or IP68 protection at a depth of 25 metres under water (a pressure of 2.5 bar) is guaranteed. The KDSU is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e. Besides the mechanical protective function offered for cables and lines, this can also be used for EMC applications.

General ordering data

Type	KDSU M32 BS O SC 1 G32
Order No.	0930041211
Version	cable glands, Brass, External thread: M 32
GTIN (EAN)	4032248917952
Qty.	10 pc(s).

Cable glands KDSU M32 BS O SC 1 G32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	105 mm	Net weight	750 g
--------	--------	------------	-------

Approvals

Approval for cable gland	ATEX II 2 GD, Ex d IIC / Ex e II / Ex tD A21 IP68, IECEX Ex d IIC / Ex e II
--------------------------	---

General information

AF size 1	46 mm	Armour, max.	2 mm
Armour, min.	0.15 mm	Cable gland	metric, brass
Explosion protection type	Pressure-resistant Ex d encapsulation, Improved safety Ex e	External thread	M 32
Inner cable diameter, max.	26.3 mm	Inner cable diameter, min.	19.5 mm
Installation guidelines	See assembly instructions	Length of thread	16 mm
Material	Brass	O-Ring	Silicone
Operating temperature range, max.	180 °C	Operating temperature range, min.	-60 °C
Outer cable diameter, max.	30.5 mm	Outer cable diameter, min.	23.2 mm
Pitch of thread	1.5	Protection degree with GWDR	IP 68 - 2.5 bar
Seal insert	Silicone	Sealing	Silicone
Size of protective cap	EL46	Type of armouring	Single-wire armouring, Metal foil armouring, Braided armouring
Water depth	25 m (30 Min.)		

Classifications

eClass 6.2	27-14-91-11	eClass 7.1	27-14-91-11
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	SIRA05ATEX1285X	Certificate No. (IECEX)	IECEXSIR05.0067X
------------------------	-----------------	-------------------------	------------------

Product information

Descriptive text ordering data	<p><0x2022> <0x0007>All cable glands have a thread pitch of 1.5 mm.</p> <p><0x2022> <0x0007>In the case of Ex d applications, the inner threads used for cable glands must meet the requirements of section 5.3 of EN/IEC 60079-1. In the screwed in position, at least 5 threads must be engaged.</p> <p><0x2022> <0x0007>If the cable glands are installed in non-metallic Ex e connection equipment, these must be connected to the protective earth of the system.</p> <p><0x2022> <0x0007>The connection cable must be laid securely and inflexibly to rule out tensile stress.</p>
--------------------------------	--

Approvals

Approvals

GOSTEX IEC EX ATEX

ROHS	Conform
------	---------

Downloads

PDF	Notice to Installers
-----	--------------------------------------

Erstellungs-Datum December 12, 2013 11:14:34 AM CET