

RF 108 OR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Flexible - More flexible - Profilform

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

General ordering data

Type	RF 108 OR
Order No.	1020690000
Version	Electronics housings orange, Clip-in foot, Width: 107.2 mm
GTIN (EAN)	4032248740154
Qty.	20 pc(s).

RF 108 OR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Length	79.2 mm	Length (inches)	3.118 inch
Width	107.2 mm	Width (inches)	4.22 inch
Height	26.2 mm	Height (inches)	1.031 inch
Net weight	8.15 g		

System characteristics

Version	Clip-in foot	Cross-connection	No
Contact to terminal rail	No	Protection degree	IP20
Encapsulation option	No		

Material data

Insulating material	PA	Colour	orange
Colour chart (similar)	RAL 2000	CTI	≥ 600
UL 94 flammability rating	V-0	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Classifications

ETIM 6.0	EC002779	eClass 6.2	27-14-91-49
eClass 7.1	27-14-91-49	eClass 8.1	27-14-91-49
eClass 9.0	27-18-27-90	eClass 9.1	27-18-27-90

Notes

Notes

Descriptive text technical data

2 optional positions for the PCB**Dimensions of the PCB:****Thickness: 1.6 (±0.2) mm, width: +0.5 mm****Dimension of RS section = PCB length - 5 mm****Example:****PCB length 160 mm, RS section = 155 mm**

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN CAT 2 PORTFOLIOGUIDE EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN
Engineering Data	STEP

Creation date May 28, 2019 2:41:26 AM CEST

Catalogue status 23.05.2019 / We reserve the right to make technical changes.