

**W-Series  
WAP WDU2.5N/4N GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | WAP WDU2.5N/4N GE          |
| Order No.  | <a href="#">1060090000</a> |
| Version    | W-Series, End plate        |
| GTIN (EAN) | 4008190097905              |
| Qty.       | 50 pc(s).                  |

## W-Series WAP WDU2.5N/4N GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 1.5 mm  | Width (inches)  | 0.059 inch |
| Height     | 44 mm   | Height (inches) | 1.732 inch |
| Depth      | 29.7 mm | Depth (inches)  | 1.169 inch |
| Net weight | 1.781 g |                 |            |

### Temperatures

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max.        | 40 °C         | Storage temperature, min.        | 10 °C  |
| Storage temperature              | 10 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C        |                                  |        |

### Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | yellow |
| UL 94 flammability rating | V-0   |        |        |

### System specifications

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

### Additional technical data

|                     |                 |         |    |
|---------------------|-----------------|---------|----|
| Installation advice | Direct mounting | Snap-on | No |
|---------------------|-----------------|---------|----|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | ETIM 4.0   | EC000886    |
| ETIM 5.0   | EC000886    | ETIM 6.0   | EC000886    |
| UNSPSC     | 30-21-18-27 | eClass 5.1 | 27-14-11-33 |
| eClass 6.2 | 27-14-11-33 | eClass 7.1 | 27-14-11-33 |
| eClass 8.1 | 27-14-11-33 | eClass 9.1 | 27-14-11-33 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data | <a href="#">STEP</a>                     |