W-Series
WSD 2.5/D-/+ WTR2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Klippon® Connect with clamping yoke Technology
The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easer and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WSD 2.5/D-/+ WTR2.5
Order No.	1058560000
Version	W-Series, Component plug, Rated cross-section: Plug-in connection, dark beige
GTIN (EAN)	4008190087371
Qty.	25 pc(s).

W-Series
WSD 2.5/D-/+ WTR2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	38.4 mm	Height (inches)	1.512 inch
Depth	29.58 mm	Depth (inches)	1.165 inch
Net weight	3.43 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	Diode module	End cover plate required	No
Number of levels	1	PE connection	No

Additional technical data

Explosion-tested version	No	Type of mounting	Plugged

Conductors for clamping (rated connection)

Connection direction	top	Type of connection	Plug-in connection

Classifications

ETIM 3.0	EC000903	ETIM 4.0	EC000903
ETIM 5.0	EC000903	ETIM 6.0	EC002018
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-27
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-11-49	eClass 9.0	27-14-11-49
eClass 9.1	27-14-11-49		

Approvals

ROHS	Conform

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP