

VSSC
VSSC4 MOV 12VDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Overvoltage protection with individual components
with varistors in terminal design

The metal-oxide varistors can be used in terminal design.
They are approved for a maximum sine-wave-form power-
frequency operating voltage, which is printed on the
component. Any voltages greater than the permitted
maximum are discharged safely within 25 ns. Varistors
are used for medium to high power.

General ordering data

Type	VSSC4 MOV 12VDC
Order No.	1063950000
Version	Surge protection for instrumentation and control, 12 V, 20 A, IEC 61643-21
GTIN (EAN)	4032248829378
Qty.	10 pc(s).

VSSC
VSSC4 MOV 12VDC
Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	6.2 mm	Width (inches)	0.244 inch
Height	76 mm	Height (inches)	2.992 inch
Depth	58.5 mm	Depth (inches)	2.303 inch
Net weight	27.8 g		

Temperatures

Humidity	5...96 %	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...80 °C		

Probability of failure

λ _{ges}	26	MTTF	4,391 Jahre
PFH in 1*10 ⁻⁹ per hour	0	SFF	100 %
SIL in compliance with IEC 61508	3		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Certificate No. (UL)	E311081	UL certificate	UL Zertifikat
----------------------	---------	----------------	---------------

CSA protection data

Gas group C	IIB	Gas group D	IIA
Gas groups A, B	IIC	Input current, max. I _i	500 mA
Input voltage, max. U _i	15 V	Internal capacity, max. C _i	12 nF
Internal inductance, max. L _i	0 μH		

General data

Colour	black	Design	Terminal
Isolating function	No	Optical function display	No
Protection degree	IP20	Rail	TS 35
Segment	Measurement - Monitoring - Setting	UL 94 flammability rating	V-0
Version	Surge protection for measurement and control		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

VSSC
VSSC4 MOV 12VDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Rated data IEC / EN**

Capacitance	11.2 nF	Discharge current $I_{\max}$ (8/20 μ s) wire-PE	1 kA
Discharge current I_n (8/20 μ s) wire-PE	0.5 kA	Discharge current, max. (8/20 μ s)	1 kA
Max. continuous voltage, U_c (DC)	15 V	Overload - failure mode	Mode 1
Protection level U_p (typ.)	≤ 100 V	Rated current I_N	20 A
Rated voltage (DC)	12 V	Requirements category acc. to IEC 61643-21	C1
Standards	IEC 61643-21	Surge current-carrying capacity C1	0.25 kA 8/20 μ s 0.5 kV 1.2/50 μ s
Surge current-carrying capacity C2	1 kA 8/20 μ s	Voltage type	AC/DC
Volume resistance	$< 0.1 \Omega$		

Further details of approvals

GOST certificate	GOST-Zertifikat
------------------	-----------------

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.8 Nm	Clamping range, min.	0.5 mm ²
Clamping range, max.	4 mm ²	Wire cross-section, solid, min.	0.5 mm ²
Wire cross-section, solid, max.	6 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	4 mm ²	Connection cross-section, stranded, min.	0.5 mm ²
Connection cross-section, stranded, max.	4 mm ²		

Ratings IECEx/ATEX/cUL

cUL certificate	cUL Certificate
-----------------	-----------------

Classifications

ETIM 3.0	EC000943	ETIM 4.0	EC000381
ETIM 5.0	EC000943	ETIM 6.0	EC000943
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-27
eClass 6.2	27-13-08-02	eClass 7.1	27-13-08-09
eClass 8.1	27-13-08-11	eClass 9.0	27-13-08-07
eClass 9.1	27-13-08-07		

Approvals

Approvals



ROHS

Conform

VSSC VSSC4 MOV 12VDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[SIL Paper](#)

[CE PAPER](#)

[Declaration of Conformity](#)

Brochure/Catalogue

[CAT 4.4 ELECTR 16/17 EN](#)

Engineering Data

[EPLAN, WSCAD](#)

Engineering Data

[STEP](#)

User Documentation

[Instruction sheet VSSC](#)


VSSC VSSC4 MOV 12VDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Similar to illustration



Circuit diagram