

**W-Series, Accessories
Q 3 WDL2.5S**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

| | |
|------------|--|
| Type | Q 3 WDL2.5S |
| Order No. | 107160000 |
| Version | W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 3 |
| GTIN (EAN) | 4008190424923 |
| Qty. | 50 pc(s). |

W-Series, Accessories Q 3 WDL2.5S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------|---------|------------|-------|
| Length | 16.2 mm | Width | 4 mm |
| Height | 9.5 mm | Net weight | 2.3 g |

Temperatures

| | |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

Additional technical data

| | | | |
|--------------------------|-------------------|---------------------|--|
| Explosion-tested version | No | Installation advice | Feed-through (bushing), Direct mounting |
| Version | For the terminals | | |

Rated data

| | |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

Material data

| | | | |
|----------|-------|--------|------|
| Material | Steel | Colour | Grey |
|----------|-------|--------|------|

System specifications

| | |
|----------------|-----------------------|
| Product family | W-Series, Accessories |
|----------------|-----------------------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000489 | UNSPSC | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 | | |

Approvals

| | |
|-----------|---------|
| Approvals | |
| ROHS | Conform |