

**W-Series
WQB PEN 16N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WQB PEN 16N
Order No.	1079600000
Version	W-Series, Cross-connector, For the terminals, No. of poles: 2
GTIN (EAN)	4008190370107
Qty.	10 pc(s).

W-Series
WQB PEN 16N
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	17.6 mm	Width (inches)	0.693 inch
Height	21.09 mm	Height (inches)	0.83 inch
Depth	1.2 mm	Depth (inches)	0.047 inch
Net weight	3.6 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Type of fixing	Plugged
----------------	---------

Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP