

Specification

Nominal Basket Diameter	10", 254mm
Nominal Impedance*	8 ohms
Power Rating**	250W
Resonance	53Hz
Usable Frequency Range***	51Hz-3.8kHz
Sensitivity	97
Magnet Weight	34 oz.
Gap Height	0.312", 7.92mm
Voice Coil Diameter	2", 50.8mm

Thiele & Small Parameters

Resonant Frequency (fs)	53Hz
DC Resistance (Re)	5.75
Coil Inductance (Le)	0.67mH
Mechanical Q (Qms)	8.14
Electromagnetic Q (Qes)	0.52
Total Q (Qts)	0.49
Compliance Equivalent Volume (Vas)	60.1 liters / 2.1 cu. ft.
Peak Diaphragm Displacement Volume (Vd)	102cc
Mechanical Compliance of Suspension (Cms)	0.36mm/N
BL Product (BL)	9.6 T-M
Diaphragm Mass inc. Airload (Mms)	25 grams
Efficiency Bandwidth Product (EBP)	103
Maximum Linear Excursion (Xmax)	3.0mm
Surface Area of Cone (Sd)	344.9 cm ²
Maximum Mechanical Limit (Xlim)	8.6mm

Mounting Information

Recommended Enclosure Volume	
Sealed	8.5-14.2 liters/0.3-0.5 cu.ft.
Vented	19.8-70.8 liters/0.7-2.5 cu.ft.
Overall Diameter	10.11", 256.8mm
Baffle Hole Diameter	9.13", 231.8mm
Front Sealing Gasket	fitted as standard
Rear Sealing Gasket	fitted as standard
Mounting Holes Diameter	0.23", 5.7mm
Mounting Holes B.C.D.	9.6", 243.8mm
Depth	3.98", 101mm
Net Weight	6.8 lbs., 3.1 kg
Shipping Weight	7.8 lbs., 3.6 kg


Materials of Construction

Aluminum voice coil
 Polyimide former
 Ferrite magnet
 Vented core
 Pressed steel basket
 Paper Cone
 Cloth cone edge
 Solid composition paper dust cap



BETA-10A American Standard Series

Recommended for professional audio, bass guitar, mid-bass or floor monitor applications in sealed enclosures.
 Also works well as a mid-bass or woofer in vented enclosures.



* Please inquire about alternative impedances.

** Multiple units exceed published rating evaluated under EIA 426A noise source and test standard while in a free-air, non-temperature controlled environment.

*** The average output across the usable frequency range when applying 1W/1M into the nominal impedance. ie: 2.83V/8ohms, 4V/16ohms.

Eminence response curves are measured under the following conditions: All speakers are tested at 1w/1m using a variety of test set-ups for the appropriate impedance | LMS using 0.25" supplied microphone (software calibrated) mounted 1m from wall/baffle | 2ft. X 2ft. baffle is built into the wall with the speaker mounted flush against a steel ring for minimum diffraction | Hafler P1500 Trans-Nova amplifier | 2700 cu.ft. chamber with fiberglass on all six surfaces (three with custom-made wedges)