

Technical Specification	
Nominal Power	=
Maximum Power	=
Freq. Response	=
S.P.L (1W/1M)	=
Impedance	=
Voice Coil	=
Cone/Surround	=
Magnet	=
Outer Diameter	A =
Mounting Hole	B =
Mounting Depth	C =

CPA15-1000	
1000 Watt	
Watt	
20 - 2,500 Hz	
98 dB	
8 Ohm	
φ100 mm	
Paper/Cloth	
220x110x25 126 oz	
φ401 mm	
φ357 mm	
160 mm	

CPA 15-400	
400 Watt	
Watt	
22 - 3,500 Hz	
98 dB	
8 Ohm	
φ75 mm	
Paper/Cloth	
190x90x20 77.7 oz	
φ385 mm	
Φ352 mm	
154 mm	

CPA 15-300	
300 Watt	
Watt	
22 - 3,500 Hz	
98 dB	
8 Ohm	
φ75 mm	
Paper/Cloth	
220x110x20 100.5 oz	
φ401 mm	
φ357 mm	
155 mm	

CPA 12-200	
200 Watt	
Watt	
35 - 4,000 Hz	
98 dB	
8 Ohm	
φ65 mm	
Paper/Cloth	
190x95x19 71.4 oz	
φ310 mm	
φ282 mm	
118.5 mm	

CPA12-150	
150 Watt	
Watt	
35 - 3,000 Hz	
96 dB	
8 Ohm	
φ65 mm	
Paper/Cloth	
156x80x20 50 oz	
φ306 mm	
φ270 mm	
123 mm	

CPA12-100FR	
100 Watt	
Watt	
35 - 6,000 Hz	
95 dB	
8 Ohm	
φ50 mm	
Paper/Cloth	
135x60x19 38.5 oz	
φ307 mm	
φ274 mm	
119 mm	

CPA10-100	
100 Watt	
Watt	
40 - 6,000 Hz	
96 dB	
8 Ohm	
φ50 mm	
Paper/Cloth	
135x60x19 38.5 oz	
φ256.5 mm	
φ226.5 mm	
105.5 mm	

Thiele/Small-Parameter

Revc (DC VC Res)	=
Fo (Res Freq)	=
Qts (Total Q)	=
Qms (Mech Q)	=
Qes (Elec Q)	=
Vas (Acous Vol)	=
Sd (Piston Area)	=
BL (Flux*Length)	=
Cms (Compliance)	=
Mms (Total Mass)	=
Mmd (Diaphm Mass)	=

5.8 ohm	
31.3276 Hz	
0.1928	
8.3144	
0.1974	
221.7425 Liter	
0.0835 sqM	
25.3583 TM	
224.1308 uMN	
115.1552 g	
101.2891 g	

5.5 ohm	
34.2831 Hz	
0.1964	
7.4451	
0.1912	
223.0437 Liter	
0.0835 sqM	
24.3400 TM	
225.4459 uMN	
95.5957 g	
81.7296 g	

5.5 ohm	
33.2682 Hz	
0.1964	
7.3340	
0.2018	
196.6294 Liter	
0.0835 sqM	
25.6123 TM	
198.7461 uMN	
115.1552 g	
101.2891 g	

6.3 ohm	
54.6218 Hz	
0.1897	
5.4561	
0.1966	
60.5274 Liter	
0.0511 sqM	
23.9037 TM	
163.4245 uMN	
51.9507 g	
45.3145 g	

6.2 ohm	
49.9130 Hz	
0.2865	
5.1500	
0.3034	
66.5006 Liter	
0.0507 sqM	
18.9002 TM	
182.3953 uMN	
55.7441 g	
49.1857 g	

7.1 ohm	
41.6782 Hz	
0.4296	
3.6313	
0.4960	
109.5160 Liter	
0.0507 sqM	
13.6296 TM	
300.3763 uMN	
48.5463 g	
41.9878 g	

7.1 ohm	
56.2881 Hz	
0.4371	
3.0115	
0.5114	
39.3960 Liter	
0.0333 sqM	
12.5389 TM	
249.6875 uMN	
32.0192 g	
28.5205 g	

Technical Specification

Nominal Power	=
Maximum Power	=
Freq. Response	=
S.P.L (1W/1M)	=
Impedance	=
Voice Coil	=
Cone/Surround	=
Magnet	=
Outer Diameter	A =
Mounting Hole	B =
Mounting Depth	C =


CPA8-100	
100 Watt	
Watt	
70 - 5,000 Hz	
96 dB	
8 Ohm	
φ50 mm	
Paper/Cloth	
135x60x19 38.5 oz	
φ208 mm	
φ179 mm	
93 mm	

CPA6-75WM	
75 Watt	
Watt	
40 - 5,000 Hz	
91 dB	
8 Ohm	
φ35 mm	
Laminated/Foam	
135x60x15 30.5 oz	
φ165.5 mm	
φ145 mm	
72.5 mm	

PA 15	
200 Watt	
400 Watt	
22 - 3,000 Hz	
96 dB	
8 Ohm	
φ65 mm	
Paper/Cloth	
156x80x20 50 oz	
φ385 mm	
φ352 mm	
154 mm	

PA 12	
150 Watt	
300 Watt	
35 - 5,000 Hz	
95 dB	
8 Ohm	
φ50 mm	
Laminated/Cloth	
140x75x20 43 oz	
φ307 mm	
φ279 mm	
115.5 mm	

PA 10	
150 Watt	
300 Watt	
40 - 5,000 Hz	
92 dB	
8 Ohm	
φ50 mm	
Laminated/Cloth	
120x60x20 30 oz	
φ255 mm	
φ235 mm	
101 mm	



Thiele/Small-Parameter

Revc (DC VC Res)	=
Fo (Res Freq)	=
Qts (Total Q)	=
Qms (Mech Q)	=
Qes (Elec Q)	=
Vas (Acous Vol)	=
Sd (Piston Area)	=
BL (Flux*Length)	=
Cms (Compliance)	=
Mms (Total Mass)	=
Mmd (Diaphm Mass)	=

7.3 ohm	
96.6785 Hz	
0.3657	
3.5706	
0.4074	
9.5258 Liter	
0.0216 sqM	
14.3515 TM	
143.2165 uMN	
18.9229 g	
17.0922 g	

7.1 ohm	
54.6218 Hz	
0.2312	
2.6268	
0.2535	
9.6214 Liter	
0.0125 sqM	
13.6854 TM	
435.7966 uMN	
19.4815 g	
18.6809 g	

5.7 ohm	
34.8021 Hz	
0.3561	
3.0115	
0.4039	
216.4407 Liter	
0.0835 sqM	
17.1765 TM	
218.7719 uMN	
95.5958 g	
81.7297 g	

7.1 ohm	
42.9497 Hz	
0.4618	
3.0115	
0.5454	
129.1623 Liter	
0.0567 sqM	
13.0588 TM	
282.8552 uMN	
48.5463 g	
40.7816 g	

7.0 ohm	
50.6696 Hz	
0.5460	
3.4649	
0.6481	
41.5183 Liter	
0.0340 sqM	
11.5745 TM	
253.2267 uMN	
38.9630 g	
35.3615 g	

