

**Clamping yoke
KLBUE 4-13.5 CPF16**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals. These are available in different versions.

General ordering data

Type	KLBUE 4-13.5 CPF16
Order No.	1167850000
Version	Clamping yoke, Clamping yoke for shield connection, Steel, 22 mm
GTIN (EAN)	4032248959655
Qty.	10 pc(s).

Clamping yoke KLBUE 4-13.5 CPF16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	22 mm	Width	20.1 mm
Height	31.45 mm	Height of lowest version	43.95 mm
Net weight	28.4 g		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	C-rail with 16-mm opening
--------------------------	----	---------------------	---------------------------

Wire clamp for cable diameter

Cable diameter, min.	4 mm	Cable diameter, max.	13.5 mm
----------------------	------	----------------------	---------

Material data

Material	Steel	Colour	Grey
----------	-------	--------	------

System specifications

Product family	Clamping yoke
----------------	---------------

Classifications

ETIM 3.0	EC000489	eClass 6.2	27-40-91-90
eClass 7.1	27-40-91-90		

Approvals

Approvals	
ROHS	Conform