

## OMNIMATE Housing - series CH20M CH20M BUS-AP RE TS 35X7.5 & 15

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



### The integrated rail bus for the modular electronics housing system

When supplying, connecting or distributing within modular applications, the rail bus can replace the tedious individual wiring process with a flexible and uninterrupted system-wide solution.

The system bus is securely integrated within the 35-mm standard mounting rail. The SMD-bus contact block can be reflow-soldered so that it can be completely automatically processed during the component assembly.

The resistant, gold-plated contact surfaces ensure a permanent and reliable contact for all housing widths.

- **Unlimited scalability** The integrated connection solution covers all system widths: from the 6-mm slice to the 67-mm large-area housing.
- **Easy to service during installation** It's easy to replace a module, even in existing modules groups – without any influence on the neighbouring modules.
- **Universal integration** The uninterrupted system bus is securely integrated within the 35-mm standard mounting rail.
- **Maximum availability** Five fully-galvanized and partially gold-plated twin-arched contacts are used to establish a permanent contact to the rail bus. THR solder flanges ensure that the connection to the circuit board is stable.

### General ordering data

|            |  |
|------------|--|
| Type       | CH20M BUS-AP RE TS 35X7.5 & 15   |
| Order No.  | <a href="#">1193170000</a>   |
| Version    | Electronics housings, OMNIMATE Housing - series CH20M , End plate, Width: 5.1 mm |
| GTIN (EAN) | 4032248987924  |
| Qty.       | 50 pc(s).  |

**Datenblatt**

**OMNIMATE Housing - series CH20M  
CH20M BUS-AP RE TS 35X7.5 & 15**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

|        |         |            |        |
|--------|---------|------------|--------|
| Length | 40.5 mm | Width      | 5.1 mm |
| Height | 9.1 mm  | Net weight | 0.67 g |

**System characteristics**

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

**Material data**

|                           |     |                     |               |
|---------------------------|-----|---------------------|---------------|
| UL 94 flammability rating | V-0 | Insulating material | Polycarbonate |
|---------------------------|-----|---------------------|---------------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| eClass 6.2 | 27-18-08-02 | eClass 7.1 | 27-18-27-02 |
|------------|-------------|------------|-------------|

**Approvals**

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |