

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Analogis Superclean**

Revision date: 20.02.2017

Product code: 6102

Page 1 of 11

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Analogis Superclean

**1.2. Relevant identified uses of the substance or mixture and uses advised against****Use of the substance/mixture**

Cleaner

**Uses advised against**

any non-intended use.

**1.3. Details of the supplier of the safety data sheet**

Company name:	Phono-Zubehör-Vertrieb GmbH	
Street:	Dyrotzer Weg 26 a	
Place:	D-14612 Falkensee	
Telephone:	03322239155	Telefax: 03322239157
e-mail:	info@tonnadel.de	
Internet:	www.analogis.eu	
Responsible Department:	Dr. Gans-Eichler Chemieberatung GmbH Raesfeldstr. 22 D-48149 Münster	e-mail: info@tge-consult.de Tel.: +49 (0)251/924520-60 www.tge-consult.de

**1.4. Emergency telephone number:**

03322239155 (This number is serviced during office hours.)

**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Regulation (EC) No. 1272/2008**

Hazard categories:

Flammable liquid: Flam. Liq. 2

Serious eye damage/eye irritation: Eye Irrit. 2

Specific target organ toxicity - single exposure: STOT SE 3

Hazard Statements:

Highly flammable liquid and vapour.

Causes serious eye irritation.

May cause drowsiness or dizziness.

**2.2. Label elements****Regulation (EC) No. 1272/2008****Hazard components for labelling**

propan-2-ol; isopropyl alcohol; isopropanol

**Signal word:**

Danger

**Pictograms:****Hazard statements**

H225

Highly flammable liquid and vapour.

H319

Causes serious eye irritation.

H336

May cause drowsiness or dizziness.

**Precautionary statements**

P101

If medical advice is needed, have product container or label at hand.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Analogis Superclean**

Revision date: 20.02.2017

Product code: 6102

Page 2 of 11

P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P235	Keep cool.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P405	Store locked up.
P501	Dispose of contents/container to local/regional/national/international regulations.

**2.3. Other hazards**

In use, may form flammable/explosive vapour-air mixture.

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

**SECTION 3: Composition/information on ingredients****3.2. Mixtures****Hazardous components**

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	Classification according to Regulation (EC) No. 1272/2008 [CLP]			
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol			85 - < 90 %
	200-661-7	603-117-00-0		
	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336			

Full text of H and EUH statements: see section 16.

**Further Information**

Product does not contain listed SVHC substances > 0,1 % according to Regulation (EC) No. 1907/2006 Article 59 (REACH)

**SECTION 4: First aid measures****4.1. Description of first aid measures****General information**

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible). Take off immediately all contaminated clothing.

First aider: Pay attention to self-protection!

**After inhalation**

Remove person to fresh air and keep comfortable for breathing. In case of respiratory tract irritation, consult a physician.

**After contact with skin**

Take off immediately all contaminated clothing. Wash with plenty of water. In case of skin irritation, seek medical treatment.

**After contact with eyes**

Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

**After ingestion**

Rinse mouth thoroughly with water. Let water be drunken in little sips (dilution effect). Do NOT induce vomiting. Never give anything by mouth to an unconscious person or a person with cramps. In all cases of doubt, or when symptoms persist, seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

No information available.

**4.3. Indication of any immediate medical attention and special treatment needed**

# Safety Data Sheet

according to Regulation (EC) No 1907/2006

## Analogis Superclean

Revision date: 20.02.2017

Product code: 6102

Page 3 of 11

Treat symptomatically.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

##### **Suitable extinguishing media**

Carbon dioxide (CO<sub>2</sub>). Dry extinguishing powder. alcohol resistant foam.  
In case of major fire and large quantities: Atomized water.

##### **Unsuitable extinguishing media**

High power water jet.

#### 5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Gas/vapours, irritant. Carbon monoxide Carbon dioxide (CO<sub>2</sub>).

#### 5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing. In case of fire and/or explosion do not breathe fumes.

#### **Additional information**

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water. Use water spray jet to protect personnel and to cool endangered containers.

In case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Remove persons to safety. Remove all sources of ignition. Ventilate affected area.

Do not breathe gas/vapour/aerosol. Avoid contact with skin, eyes and clothes.

Wear personal protection equipment. (See section 8.)

#### 6.2. Environmental precautions

Do not allow to enter into surface water or drains. Danger of explosion! Cover drains. Prevent spread over a wide area (e.g. by containment or oil barriers). In case of gas escape or of entry into waterways, soil or drains, inform the responsible authorities.

#### 6.3. Methods and material for containment and cleaning up

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents). Ventilate affected area.

Treat the recovered material as prescribed in the section on waste disposal.

Clean contaminated objects and areas thoroughly observing environmental regulations.

#### 6.4. Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

##### **Advice on safe handling**

Provide adequate ventilation as well as local exhaustion at critical locations.

Professional: Use only outdoors or in a well-ventilated area.

Wear suitable protective clothing. (See section 8.)

##### **Advice on protection against fire and explosion**

Keep away from sources of ignition. - No smoking. Take precautionary measures against static discharges.

Flammable vapours can accumulate in head space of closed systems. In use, may form flammable/explosive vapour-air mixture. Heating causes rise in pressure with risk of bursting.

##### **Further information on handling**

Do not breathe gas/vapour/aerosol. Avoid contact with skin, eyes and clothes.

# Safety Data Sheet

according to Regulation (EC) No 1907/2006

## Analogis Superclean

Revision date: 20.02.2017

Product code: 6102

Page 4 of 11

General protection and hygiene measures: See section 8.

### 7.2. Conditions for safe storage, including any incompatibilities

#### Requirements for storage rooms and vessels

Keep container tightly closed in a cool, well-ventilated place. Protect against direct sunlight.

Ensure adequate ventilation of the storage area.

Make sure spills can be contained (e.g. sump pallets or kerbed areas).

#### Advice on storage compatibility

Do not store together with: Gas. Explosives. Flammable solids. Pyrophoric liquids and solids. Self-heating substances and mixtures. Substances and mixtures which, in contact with water, emit flammable gases.

Oxidizing liquids. Oxidizing solids. ammonium nitrate. Self-reactive substances and mixtures. Organic peroxides. Non-combustible toxic substances. Radioactive substances. Infectious substances.

#### Further information on storage conditions

Keep the packing dry and well sealed to prevent contamination and absorption of humidity.

Protect against: UV-radiation/sunlight. heat. moisture. frost.

storage temperature: 15-25°C

### 7.3. Specific end use(s)

refer to chapter 1.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits (EH40)

CAS No	Substance	ppm	mg/m <sup>3</sup>	fibres/ml	Category	Origin
67-63-0	Propan-2-ol	400	999		TWA (8 h)	WEL
		500	1250		STEL (15 min)	WEL

### 8.2. Exposure controls



#### Appropriate engineering controls

Provide adequate ventilation as well as local exhaust at critical locations.

Professional: Use only outdoors or in a well-ventilated area.

#### Protective and hygiene measures

The usual precautions for handling chemicals should be considered.

Keep away from food, drink and animal feedingstuffs.

Always close containers tightly after the removal of product. When using do not eat, drink, smoke, sniff. Wash hands before breaks and after work. Protect skin by using skin protective cream. Take off contaminated clothing and wash it before reuse.

#### Eye/face protection

Recommended eye protection brand: Tightly sealed safety glasses. (DIN EN 166)

#### Hand protection

In case of prolonged or frequently repeated skin contact: Wear suitable gloves.

Suitable material:

Butyl rubber.

Thickness of glove material: 0,5 mm

penetration time (maximum wearing period): 480 min.

NBR (Nitrile rubber)

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Analogis Superclean**

Revision date: 20.02.2017

Product code: 6102

Page 5 of 11

Thickness of glove material: 0,35 mm  
penetration time (maximum wearing period): 480 min.

FKM (fluoro rubber)

Thickness of glove material: 0,4 mm  
penetration time (maximum wearing period): 480 min.

In the case of wanting to use the gloves again, clean them before taking off and air them well. Before using check leak tightness / impermeability.

For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

**Skin protection**

Wear fire/flare resistant/retardant clothing.

Minimum standard for preventive measures while handling with working materials are specified in the TRGS 500.

**Respiratory protection**

With correct and proper use, and under normal conditions, breathing protection is not required.

Respiratory protection necessary at:

exceeding exposure limit values

insufficient ventilation.

Suitable respiratory protective equipment: gas filtering equipment (EN 141). Type: A

The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used. Observe the wear time limits according GefStoffV in combination with the rules for using respiratory protection apparatus (BGR 190).

**Environmental exposure controls**

Do not allow uncontrolled discharge of product into the environment.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Physical state:	liquid.
Colour:	not determined
Odour:	characteristic

**Test method**

pH-Value:	not determined
-----------	----------------

**Changes in the physical state**

Melting point:	not applicable
----------------	----------------

Initial boiling point and boiling range:	82 °C
--	-------

Flash point:	0-<21 °C
--------------	----------

**Explosive properties**

In use, may form flammable/explosive vapour-air mixture.

Lower explosion limits:	not determined
-------------------------	----------------

Upper explosion limits:	not determined
-------------------------	----------------

Ignition temperature:	not determined
-----------------------	----------------

Decomposition temperature:	not determined
----------------------------	----------------

**Oxidizing properties**

none.

Vapour pressure: (at 20 °C)	not determined
--------------------------------	----------------

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Analogis Superclean**

Revision date: 20.02.2017

Product code: 6102

Page 6 of 11

Density:	not determined
Water solubility:	miscible.
<b>Solubility in other solvents</b>	
not determined	
Partition coefficient:	not determined
Viscosity / dynamic: (at 20 °C)	not determined
Viscosity / kinematic: (at 20 °C)	not determined
Flow time:	not determined
Vapour density:	not determined
Evaporation rate:	not determined
Solvent separation test:	not determined
Solvent content:	not determined

**9.2. Other information**

Solid content:	not determined
----------------	----------------

**SECTION 10: Stability and reactivity****10.1. Reactivity**

No information available.

**10.2. Chemical stability**

The mixture is chemically stable under recommended conditions of storage, use and temperature.

**10.3. Possibility of hazardous reactions**

No information available.

**10.4. Conditions to avoid**

Keep away from heat. Ignition hazard!  
In use may form flammable/explosive vapour-air mixture.  
Heating causes rise in pressure with risk of bursting.

**10.5. Incompatible materials**

Materials to avoid: Oxidizing agents, strong. Reducing agents, strong. Strong acid. strong alkalis.

**10.6. Hazardous decomposition products**Can be released in case of fire: Gas/vapours, irritant. Carbon monoxide Carbon dioxide (CO<sub>2</sub>).**SECTION 11: Toxicological information****11.1. Information on toxicological effects****Toxicokinetics, metabolism and distribution**

No data available.

**Acute toxicity**

Based on available data, the classification criteria are not met.

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol				
	oral	LD50 mg/kg	>5000	Rat	ECHA Dossier

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Analogis Superclean**

Revision date: 20.02.2017

Product code: 6102

Page 7 of 11

**Irritation and corrosivity**

Causes serious eye irritation.

Skin corrosion/irritation: Based on available data, the classification criteria are not met.

**Sensitising effects**

Based on available data, the classification criteria are not met.

**Carcinogenic/mutagenic/toxic effects for reproduction**

Based on available data, the classification criteria are not met.

Isopropyl alcohol. (CAS-No.: 67-63-0):

In-vitro mutagenicity: No experimental indications of mutagenicity in-vitro exist.

Carcinogenicity :

Exposure time: 24 month

Species: Fischer 344 Rat.

Method: OECD Guideline 451

Result: NOEL = 5000 ppm

Literature information: ECHA Dossier

**STOT-single exposure**

May cause drowsiness or dizziness. ( (propan-2-ol; isopropyl alcohol; isopropanol))

**STOT-repeated exposure**

Based on available data, the classification criteria are not met.

Isopropyl alcohol. (CAS-No.: 67-63-0):

Chronic inhalative toxicity

Exposure time: 24 month

Species: Fischer 344 Rat.

Method: OECD Guideline 451

Result: NOAEC = 5000 ppm

Literature information: ECHA Dossier

**Aspiration hazard**

Based on available data, the classification criteria are not met.

**Specific effects in experiment on an animal**

No data available.

**SECTION 12: Ecological information****12.1. Toxicity**

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h]   [d]	Species	Source	Method
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol					
	Acute fish toxicity	LC50 mg/l	9640	96 h	Pimephales promelas	ECHA Dossier

**12.2. Persistence and degradability**

CAS No	Chemical name				
	Method	Value	d	Source	
	Evaluation				
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol				
	EU Method C.5/ EU Method C.6	53%	5	ECHA Dossier	
	Product is biodegradable.				

**12.3. Bioaccumulative potential**

# Safety Data Sheet

according to Regulation (EC) No 1907/2006

## Analogis Superclean

Revision date: 20.02.2017

Product code: 6102

Page 8 of 11

### Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol	0,05

### 12.4. Mobility in soil

No data available.

### 12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

### 12.6. Other adverse effects

No data available.

### Further information

Do not allow to enter into surface water or drains.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

#### Advice on disposal

Dispose of waste according to applicable legislation. Consult the local waste disposal expert about waste disposal. Non-contaminated packages may be recycled. According to EAKV, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process.

Control report for waste code/ waste marking according to EAKV:

#### Waste disposal number of waste from residues/unused products

200129 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); detergents containing hazardous substances  
Classified as hazardous waste.

#### Waste disposal number of used product

200129 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); detergents containing hazardous substances  
Classified as hazardous waste.

#### Waste disposal number of contaminated packaging

150110 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); packaging containing residues of or contaminated by hazardous substances  
Classified as hazardous waste.

#### Contaminated packaging

Handle contaminated packages in the same way as the substance itself.

## SECTION 14: Transport information

### Land transport (ADR/RID)

<b>14.1. UN number:</b>	UN 1219
<b>14.2. UN proper shipping name:</b>	ISOPROPANOL (ISOPROPYL ALCOHOL)
<b>14.3. Transport hazard class(es):</b>	3
<b>14.4. Packing group:</b>	II
Hazard label:	3





## Safety Data Sheet

according to Regulation (EC) No 1907/2006

## Analogis Superclean

Revision date: 20.02.2017

Product code: 6102

Page 9 of 11

Classification code: F1  
 Special Provisions: 601  
 Limited quantity: 1 L  
 Excepted quantity: E2  
 Transport category: 2  
 Hazard No: 33  
 Tunnel restriction code: D/E

## Inland waterways transport (ADN)

**14.1. UN number:** UN 1219  
**14.2. UN proper shipping name:** ISOPROPANOL (ISOPROPYL ALCOHOL)  
**14.3. Transport hazard class(es):** 3  
**14.4. Packing group:** II  
 Hazard label: 3



Classification code: F1  
 Special Provisions: 601  
 Limited quantity: 1 L  
 Excepted quantity: E2

## Marine transport (IMDG)

**14.1. UN number:** UN 1219  
**14.2. UN proper shipping name:** ISOPROPANOL (ISOPROPYL ALCOHOL)  
**14.3. Transport hazard class(es):** 3  
**14.4. Packing group:** II  
 Hazard label: 3



Marine pollutant: NO  
 Special Provisions: -  
 Limited quantity: 1 L  
 Excepted quantity: E2  
 EmS: F-E, S-D

## Air transport (ICAO-TI/IATA-DGR)

**14.1. UN number:** UN 1219  
**14.2. UN proper shipping name:** ISOPROPANOL (ISOPROPYL ALCOHOL)  
**14.3. Transport hazard class(es):** 3  
**14.4. Packing group:** II  
 Hazard label: 3



Special Provisions: A180  
 Limited quantity Passenger: 1 L  
 Passenger LQ: Y341  
 Excepted quantity: E2  
 IATA-packing instructions - Passenger: 353

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Analogis Superclean**

Revision date: 20.02.2017

Product code: 6102

Page 10 of 11

IATA-max. quantity - Passenger:	5 L
IATA-packing instructions - Cargo:	364
IATA-max. quantity - Cargo:	60 L

**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: no

**14.6. Special precautions for user**

See section 8.

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not relevant.

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

2010/75/EU (VOC):	No information available.
2004/42/EC (VOC):	No information available.
Information according to 2012/18/EU (SEVESO III):	P5c FLAMMABLE LIQUIDS

**Additional information**

The mixture is classified as hazardous according to regulation (EC) No 1272/2008 [CLP].  
REACH 1907/2006 Appendix XVII, No: 3

**National regulatory information**

Employment restrictions:	Observe restrictions to employment for juvenils according to the 'juvenile work protection guideline' (94/33/EC).
Water contaminating class (D):	2 - water contaminating

**15.2. Chemical safety assessment**

Chemical safety assessments for substances in this mixture were not carried out.

**SECTION 16: Other information****Changes**

Rev. 1.00; 20.02.2017, Initial release

**Abbreviations and acronyms**

ADR: Accord européen sur le transport des marchandises dangereuses par Route  
CAS Chemical Abstracts Service  
DNEL: Derived No Effect Level  
IARC: INTERNATIONAL AGENCY FOR RESEARCH ON CANCER  
International Carriage of Dangerous Goods by Road)  
IMDG: International Maritime Code for Dangerous Goods  
IATA: International Air Transport Association  
IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)  
ICAO: International Civil Aviation Organization  
ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)  
GHS: Globally Harmonized System of Classification and Labelling of Chemicals  
GefStoffV: Gefahrstoffverordnung (Ordinance on Hazardous Substances, Germany)  
LOAEL: Lowest observed adverse effect level  
LOAEC: Lowest observed adverse effect concentration  
LC50: Lethal concentration, 50 percent  
LD50: Lethal dose, 50 percent  
NOAEL: No observed adverse effect level  
NOAEC: No observed adverse effect level

## Safety Data Sheet

according to Regulation (EC) No 1907/2006

### Analogis Superclean

Revision date: 20.02.2017

Product code: 6102

Page 11 of 11

NTP: National Toxicology Program

N/A: not applicable

OSHA: Concerning the International Transport of Dangerous Goods by Rail )

PNEC: predicted no effect concentration

PBT: Persistent bioaccumulative toxic

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail )

SARA: Superfund Amendments and Reauthorization Act

SVHC: substance of very high concern

TRGS Technische Regeln für Gefahrstoffe

TSCA: Toxic Substances Control Act

VOC: Volatile Organic Compounds

VwVwS: Verwaltungsvorschrift wassergefährdender Stoffe

WGK: Wassergefährdungsklasse

#### Relevant H and EUH statements (number and full text)

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

#### Further Information

Classification according EC regulation 1272/2008 (CLP): - Classification procedure:

Health hazards: Calculation method.

Environmental hazards: Calculation method.

Physical hazards: On basis of test data. and / or calculated and / or estimated.

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

---

*(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)*