
# Conductor markers
# CLI C 2-4 RT/SW 2 CD

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

## General ordering data

| | |
|---|---|
| Type | CLI C 2-4 RT/SW 2 CD |
| Order No. | 1568261509 |
| Version | Conductor markers, 4 x 7 mm, PVC, soft, without Cadmium, Colour: Red |
| GTIN (EAN) | 4008190916206 |
| Qty. | 250 pc(s). |

# Conductor markers
# CLI C 2-4 RT/SW 2 CD

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technische Daten

### Dimensions and weights

| | | | |
|---|---|---|---|
| Length | 4 mm | Width | 7 mm |
| Height | 8 mm | Depth | 8 mm |
| Net weight | 0.206 g | | |

### General data

| | | | |
|---|---|---|---|
| Colour | Red | Colour of printing | White |
| Insulation cross-section, max. | 10 mm | Material | PVC, soft, without Cadmium |
| Material colour according to resistance code | 2 | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Orientation of print | horizontal |
| Printed characters | Numbers | Printing | 2 |
| Printing method | Laser print | Recommended industries | Process, Machinery |
| Type of printing | Standard | UL 94 flammability rating | V-0 |

### Conductor and cable markers

| | | | |
|---|---|---|---|
| Conductor O.D., max. | 10 mm | Conductor O.D., min. | 4 mm |
| Conductor cross-section, max. | 16 mm² | Conductor cross-section, min. | 2.5 mm² |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 3.0 | EC001530 | UNSPSC | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 | | |

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

# Conductor markers
# CLI C 2-4 RT/SW 2 CD

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Zeichnungen




Product is similar to illustration