

Cable glands VG 21-K68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Screwed joints that comply with the high demands of
class of protection IP 68

General ordering data

Type	VG 21-K68
Order No.	1569020000
Version	cable glands, Polyamide 6, RAL 7035, External thread: PG 21
GTIN (EAN)	4008190032234
Qty.	25 pc(s).

Cable glands VG 21-K68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	48 mm	Net weight	20.8 g
--------	-------	------------	--------

General information

AF size 1	33 mm	Cable gland	PG
Clamping range, max.	18 mm	Clamping range, min.	13 mm
Colour code	RAL 7035	DIN	EN 50262 (for M thread)
External thread	PG 21	Length of thread	11 mm
Material	Polyamide 6	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Seal insert	CR
Torque for cap nut, max.	6 Nm	Torque for cap nut, min.	5 Nm
Torque for connecting adapter, max.	9 Nm	Torque for connecting adapter, min.	7 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Long-thread version on request, halogen-free without sealing ring
Descriptive text technical data	Version with moulded sealing lip Length L varies depending on the cable diameter used

Approvals

Approvals



ROHS	Conform
------	---------