



IT-400TW

Order No.: 16.2580

PRODUCTINFOS

The music horns from MONACOR are the state-of-the-art solution in order to use the full range of a horn speaker with a clearly extended frequency range.

The 2-way technology with a dynamic cone bass-midrange speaker and a horn tweeter allows for an increase in the sound quality and permits to radiate the keynotes of voices and instruments which cannot be achieved by conventional horn speakers. The music horns are a perfect solution whenever an optimum voice volume and/or a more complete music transmission is required.

Weatherproof horn speaker (music horn), 2-way technology

- 100 V line technique with very high tapping power
- Weatherproof and IP66 certified
- Very wideband sound with a distinct bass volume, even at very high volume levels
- 16 cm bass-midrange speaker and 25 mm (1") horn
- Robust plastic housing
- Supplied with mounting bracket and screws made of stainless steel


TECHNICAL SPECIFICATIONS

IT-400TW


Impedance	-
Operating voltage	100V
Power rating	60/30/15/7.5 W
Peak music power output	-
Frequency range	100-15000Hz
Sensitivity	101dB/W/m
Radiation angle, horizontal	100°
Radiation angle, vertical	60°
Material (housing/cabinet)	ABS
Protective class	IP66
Weather resistance	yes
Mounting facility	stainless steel mounting bracket
Features	2-way
Replacement voice coil	-
Admiss. ambient temp.	-20 °C to +50 °C
Dimensions	420 x 335 x 400 mm
Weight	6,7kg

* **Important Notice:** The retail prices shown here are non-binding recommendations that retailers can charge their customers. They are not part of any specific offer or advertisement. These prices include all charges as well as VAT, but do not cover any additional delivery and shipping costs. Our latest price lists for the retail market include all applicable delivery and payment terms for retailers.

Frequency Response



Polor Diagram /Horizontal



Polor Diagram /Vertical

