

**RIDERSERIES  
RCM570548**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Standard relays in the RIDERSERIES RCM

- 4 CO contacts
- Optionally AC or DC coils
- with test button
- Comes optionally with integrated status display and/or free-wheel diode

**General ordering data**

Type	RCM570548
Order No.	<a href="#">1180900000</a>
Version	RIDERSERIES, Relais, No. of contacts: 4, CO contact with test button, AgNi 90/10, Rated control voltage: 48 V AC, Continuous current: 6 A, Plug-in connection
GTIN (EAN)	4008190172978
Qty.	10 pc(s).

## RIDERSERIES RCM570548

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	22.5 mm	Height	28 mm
Depth	29 mm	Weight	30 g
Net weight	30.8 g		

### Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature	-40 °C...+70 °C
Storage temperature	-40 °C...+85 °C		

### Input

Coil resistance	777 Ω ± 10 %	Pull-inrop-out current, typ.	
Rated control voltage	48 V AC	Rated current AC	21.3 mA
Power rating	1.0 VA	Pull-inrop-out typ.	38.4 V / 14.4 V AC

### Output

Rated switching voltage	240 V AC	Max. switching voltage, AC	240 V
Continuous current	6 A	Inrush current	12 A / 20 ms
Max. switching power	1500 VA	Switch-on delay	≤ 15 ms
Switch-off delay	≤ 10 ms	Duration of Bounce	5 ms
Min. switching power	100 mA / 5 V, 10 V / 10 mA, 24 V / 1 mA	Max. switching frequency at rated load	0.1 Hz

### Contact data

No. of contacts	4	Contact design	CO contact with test button
Contact material	AgNi 90/10	Mechanical service life	AC coil 20 x 10 <sup>6</sup> Switching cycles, DC coil 30 x 10 <sup>6</sup> Switching cycles

### General data

Test button	Yes	Wire connection method	Plug-in connection
Humidity	40 °C / 93 % rel. humidity, no condensation	Weight	30 g
UL 94 flammability rating	V-0		

### Insulation coordination

Creepage and clearance distance input - output	≥ 4 mm	Dielectric strength input - output	2.5 kV <sub>eff</sub>
Dielectric strength, contact contact	2 kV <sub>eff</sub>	Rated voltage	250 V
Impulse withstand voltage	5 kV (1.2/50 μs)	Protection degree	IP 50
Insulating material group	IIIa	Pollution severity	2
Surge voltage category	III		

### Other technical data

Version	Without LED
---------	-------------

**Datenblatt**

**RIDERSERIES  
RCM570548**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Further details of approvals / standards**

Standards IEC 61810-1, UL508

**Connection data**

Wire connection method Plug-in connection

**Classifications**

ETIM 3.0	EC001437	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-01	eClass 6.2	27-37-16-01
eClass 7.1	27-37-16-01		

**Approvals**

Approvals




ROHS Conform


**Downloads**

Declaration of Conformity [K295\\_02\\_13.pdf](#)


**Electric symbol**



**DC load breaking capacity**



**Operating voltage range AC**



**Electrical endurance**

