


**RS 100
AP 100 D BK**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

**Flexible - More flexible - Profilform**

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

General ordering data

Type	AP 100 D BK
Order No.	1189870000
Version	Electronics housings, RS 100 black, End plate, Width: 21.5 mm
GTIN (EAN)	4050118159936
Qty.	20 pc(s).

Data sheet

RS 100
AP 100 D BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	108.2 mm	Length (inches)	4.26 inch
Width	21.5 mm	Width (inches)	0.846 inch
Height	21.9 mm	Height (inches)	0.862 inch
Net weight	6.8 g		

System characteristics

Version	End plate	Cross-connection	No
Contact to terminal rail	No	Protection degree	IP20
Encapsulation option	No		

Material data

Insulating material	PA 66	Colour	black
Colour chart (similar)	RAL 9011	CTI	≥ 600
UL 94 flammability rating	V-2	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Classifications

ETIM 5.0	EC000886	ETIM 6.0	EC001031
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-18-27-90
eClass 9.1	27-18-27-90		

Notes

Notes

Descriptive text technical data

3 heights are available for the cover profile and the end plates:

TS mounting without cover: TS 32 = 45 mm, TS35x7.5 = 40.5 mm

TS mounting with low cover: TS 32 = 89 mm, TS 35x7.5 = 84.5 mm

TS mounting with high cover: TS 32 = 121 mm, TS 35x7.5 = 116.5 mm

Direct mounting, without/low/high cover: 24 / 69 / 99 mm

Dimensions of the PCB

Thickness: 1.6 (±0.2) mm, width: 100 (+0.5) mm

Dimension of the RS section = length of the printed circuit board - 4.5 mm

Dimension of ADP section = PCB length - 1 mm

Example:

PCB length 160 mm, RS = 155.5 mm, ADP = 159 mm

Approvals

ROHS Conform

Data sheet**RS 100**
AP 100 D BK**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Technical data****Downloads**

Brochure/Catalogue	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN
Engineering Data	EPLAN

Data sheet

**RS 100
AP 100 D BK**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

DIRECT MOUNTING
 FOR BOTH SIDES (RIGHT AND LEFT)

