

Accessories
VGM40/1-MS68 20-32 BG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Currently, heavy-duty connectors are used wherever there is a need for a secure, simple and time-saving assembly of machinery and facilities.

The connector housings are made of die-cast aluminium and offer excellent protection against dirt, moisture and mechanical stress.

Special modular connectors make it possible to integrate signals, power supply, pneumatics, and data connections into a single connector.

With the RockStar® heavy-duty connectors, Weidmüller offers a product line with many patented innovations that is oriented towards the future.

The RockStar® product line defines new standards with the comprehensive depth and width of its features. What other suppliers offer only as a custom configuration, Weidmüller supplies in its standard product line.

As a result, selecting the proper connector is now easier than ever. You save both time and money. And your work flow is optimised. Thus you can strengthen your position on the market and leverage your competitive advantage

General ordering data

Type	VGM40/1-MS68 20-32 BG
Order No.	1205890000
Version	Heavy Duty Connectors, Accessories, cable glands, Brass, nickel-plated
GTIN (EAN)	4032248987818
Qty.	10 pc(s).

Accessories VGM40/1-MS68 20-32 BG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	82 mm	Net weight	340 g
--------	-------	------------	-------

Temperatures

Operating temperature	-30 °C...+100 °C
-----------------------	------------------

General data

AF size	45 mm	Cable diameter, max.	32 mm
Cable diameter, min.	20 mm	Cable gland	M 40
External thread	M 40	Length of thread	8 mm
Material	Brass, nickel-plated	O-Ring	NBR
Protection degree	IP 68	Sealing material	TPE
Tightening torque, max.	20 Nm	Type of sealing	Rubber ring

Classifications

eClass 6.2	27-18-92-34	eClass 7.1	27-18-92-34
------------	-------------	------------	-------------

Approvals

Approvals



ROHS	Conform
------	---------