

**P-series
PPV 4 OR 35X15 DGR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Save space by connecting with these multi-tier terminals with PUSH IN connection technology.

The product line includes the four-channel, eight-channel and also the innovative sixteen-channel feed-through terminal blocks. The four-channel and eight-channel terminals are also available as potential distribution terminals.

The benefits:

- More than 1700 signals per metre can be distributed with the 16-channel terminal block.
- Red and white actuators make it easier to assign wires to their terminal points.
- The PUSH IN connections make wiring quick and convenient.

General ordering data

Type	PPV 4 OR 35X15 DGR
Order No.	1301610000
Version	P-series, Potential distributor, Rated cross-section: 1.5 mm ² , Number of levels: 4, Number of connections: 16, Colour: orange
GTIN (EAN)	4050118098778
Qty.	20 pc(s).

P-series PPV 4 OR 35X15 DGR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	9.2 mm	Width (inches)	0.362 inch
Height	70 mm	Height (inches)	2.756 inch
Depth	54.5 mm	Depth (inches)	2.146 inch
Net weight	21.91 g		

Temperatures

Storage temperature, max.	70 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...70 °C	Temperature range, installation, min.	-10 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	130 °C
Temperature range, installation, max.	40 °C		

Material data

Material	Polycarbonate	Material of operational elements	PBT
Colour	orange	UL 94 flammability rating	V-0

System specifications

Version	PUSH IN connection, Vertically cross-connected, One end without connector	End cover plate required	Yes
Number of levels	4	No. of clamping points per level	4
Number of potentials per tier	1	Levels cross-connected internally	Yes
PE connection	No	Rail	TS 35 x 15

Additional technical data

Type of mounting	Snap-on
------------------	---------

Conductors for clamping (rated connection)

Blade size	0.6 x 3.5 mm	Clamping range, max.	1.5 mm ²
Clamping range, min.	0.13 mm ²	Connection cross-section, stranded, max.	1.5 mm ²
Connection cross-section, stranded, min.	0.5 mm ²	Connection direction	Inclined / angled
Number of connections	16	Stripping length	10 mm
Type of connection	PUSH IN	Wire connection cross section AWG, max.	AWG 16
Wire connection cross section AWG, min.	AWG 24	Wire connection cross section, finely stranded, max.	1.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²
Wire connection cross-section, finely stranded, min.	0.5 mm ²	Wire connection cross-section, solid core, max.	1.5 mm ²
Wire connection cross-section, solid core, min.	0.5 mm ²		

P-series
PPV 4 OR 35X15 DGR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Rating data

Rated cross-section	1.5 mm ²	Rated voltage	250 V
Rated current	17.5 A	Standards	IEC 60947-7-1, DIN EN 60079
Volume resistance according to IEC 60947-7-x	1.83 mΩ	Rated impulse withstand voltage	4 kV
Pollution severity	3	Surge voltage category	III

UL rating data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	16 AWG
Conductor size Factory wiring min. (cURus)	26 AWG	Conductor size Field wiring max. (cURus)	16 AWG
Conductor size Field wiring min. (cURus)	26 AWG	Current size B (cURus)	10 A
Current size D (cURus)	10 A	Voltage size B (cURus)	300 V
Voltage size D (cURus)	300 V		

Classifications

ETIM 5.0	EC000897	ETIM 6.0	EC000897
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-24	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	DE_PT1441_20160418_297_ISSUE01.pdf
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	Beipackzettel_PRV_PPV.pdf

Safety note

 Safety notice [Safety Information](#)

P-series PPV 4 OR 35X15 DGR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

