

**Cable markers  
SFX-M 11/60 AL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

A special punching in the SFX-M allows the use of steel cable ties.

**General ordering data**

|            |                                                   |
|------------|---------------------------------------------------|
| Type       | SFX-M 11/60 AL                                    |
| Order No.  | <a href="#">1327780000</a>                        |
| Version    | Cable markers, MetalliCard, 60 x 11 mm, Aluminium |
| GTIN (EAN) | 4050118132649                                     |
| Qty.       | 50 pc(s).                                         |

**Cable markers  
SFX-M 11/60 AL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Technische Daten****Dimensions and weights**

|        |        |            |         |
|--------|--------|------------|---------|
| Length | 60 mm  | Width      | 11 mm   |
| Height | 0.8 mm | Net weight | 0.834 g |

**General data**

|                                   |           |                                   |                 |
|-----------------------------------|-----------|-----------------------------------|-----------------|
| Material                          | Aluminium | Operating temperature range, max. | 130 °C          |
| Operating temperature range, min. | -55 °C    | Recommended industries            | Process, Energy |

**Conductor and cable markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|            |             |
|------------|-------------|
| eClass 6.2 | 27-14-91-29 |
|------------|-------------|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                                 |                                        |
|---------------------------------|----------------------------------------|
| M-Print® PRO configuration file | <a href="#">mc_sfx-m_11_60_mcf.zip</a> |
|---------------------------------|----------------------------------------|