

**VG MS (standard brass cable gland)
VG 36-MS68****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Screwed joints that comply with the high demands of
class of protection IP 68

General ordering data

Type	VG 36-MS68
Order No.	1569130000
Version	VG MS (standard brass cable gland), Cable glands, PG 36, 9 mm, OD min. 22 - OD max. 32 mm, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
GTIN (EAN)	4008190148263
Qty.	5 pc(s).

VG MS (standard brass cable gland) VG 36-MS68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	57 mm	Length (inches)	2.244 inch
Net weight	253.77 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

AF size 1	50 mm	AF size 2	50 mm
Cable glands	PG	Clamp insert	Polyamide
External thread	PG 36	Length of thread	9 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
Protection degree	IP67, IP68 - 5 bar (30 min.)	Protection degree with GWDR	IP67, IP68 - 5 bar (30 min.)
Seal insert	CR	Sealing	NBR
Torque for cap nut, max.	41.5 Nm	Torque for cap nut, min.	38.5 Nm
Torque for connecting adapter, max.	22 Nm	Torque for connecting adapter, min.	18 Nm

Classifications

ETIM 3.0	EC000441	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-09
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP