

## Device markers ESG 9/20 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

### General ordering data

|            |  |
|------------|--|
| Type       | ESG 9/20 MC NE WS  |
| Order No.  | <a href="#">1609940000</a>   |
| Version    | Device markers, MultiCard, 20 x 9 mm, Polyamide 66, Colour: White, pluggable |
| GTIN (EAN) | 4008190203528  |
| Qty.       | 200 pc(s).   |

## Device markers ESG 9/20 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |         |
|--------|--------|------------|---------|
| Length | 20 mm  | Width      | 9 mm    |
| Height | 0.8 mm | Net weight | 0.545 g |

### General data

|                                   |                                      |  |        |
|-----------------------------------|--------------------------------------|--|--------|
| Application/manufacturere         | Siemens, Moeller, WI SAI distributor | Colour                                       | White  |
| Material                          | Polyamide 66                         | Material colour according to resistance code | 9      |
| Operating temperature range, max. | 100 °C                               | Operating temperature range, min.            | -40 °C |
| UL 94 flammability rating         | V-2                                  |  |        |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001288    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |  |
|---------------------------------|--|
| M-Print® PRO configuration file | <a href="#">mc_esg_9_20_mcf.zip</a>                  |
| DXF                             | <a href="#">20847_ESG_9-20_MC_DXF.dxf</a>            |
| STEP                            | <a href="#">1609940000_20847_ESG-9x20-MC_STP.stp</a> |

**Datenblatt**

**Device markers**  
**ESG 9/20 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Example of use**



**Drawing**

