Conductor markers
TM-I 15 MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

General ordering data

Type	TM-I 15 MC NE RT
Order No.	1609981686
Version	Conductor markers, MultiCard, 15 x 4 mm, Polyamide 66, Colour: Red
GTIN (EAN)	4008190367824
Qty.	400 pc(s).

Conductor markers
TM-I 15 MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	15 mm	Width	4 mm
Height	2 mm	Depth	2 mm
Net weight	0.273 g		

General data

Colour	Red	Material	Polyamide 66
Material colour according to resistance code	2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Recommended industries	Transportation, Machinery
Type of printing	blank	UL 94 flammability rating	V-2

Conductor and cable markers

Conductor O.D., max.	40 mm	Conductor O.D., min.	1 mm
Conductor cross-section, max.	500 mm²	Conductor cross-section, min.	0.22 mm²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_tm-i_15_mcf.zip