


## Cable markers LM WRITE ON 18X34 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



LM WriteOn cable markers on DIN A4 sheets are used for labelling conductors and cables up to an outside diameter of 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Easy and quick labelling with a DIN A4 laser printer or STI pen

### General ordering data

|            |                                                                  |
|------------|------------------------------------------------------------------|
| Type       | LM WRITE ON 18X34 GE                                             |
| Order No.  | <a href="#">1695711687</a>                                       |
| Version    | Cable markers, Label, 34 x 18 mm, Polyester film, Colour: Yellow |
| GTIN (EAN) | 4008190924669                                                    |
| Qty.       | 10 pc(s).                                                        |

## Cable markers LM WRITE ON 18X34 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |        |
|--------|--------|------------|--------|
| Length | 34 mm  | Width      | 18 mm  |
| Depth  | 0.2 mm | Net weight | 10.2 g |

### General data

|                                   |                |                                              |              |
|-----------------------------------|----------------|----------------------------------------------|--------------|
| Adhesive                          | Acrylate       | Colour                                       | Yellow       |
| Material                          | Polyester film | Material colour according to resistance code | 4            |
| Number per sheet                  | 88             | Operating temperature range, max.            | 150 °C       |
| Operating temperature range, min. | -40 °C         | Size of labelling field                      | 18 x 12.7 mm |
| Type of printing                  | blank          | UL 94 flammability rating                    | HB           |

### Conductor and cable markers

|                               |                    |                               |                   |
|-------------------------------|--------------------|-------------------------------|-------------------|
| Conductor O.D., max.          | 7 mm               | Conductor O.D., min.          | 5 mm              |
| Conductor cross-section, max. | 16 mm <sup>2</sup> | Conductor cross-section, min. | 6 mm <sup>2</sup> |
| Halogen                       | No                 |                               |                   |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                               |
|---------------------------------|-----------------------------------------------|
| M-Print® PRO configuration file | <a href="#">lab_lm_write_on_18x34_mcf.zip</a> |
|---------------------------------|-----------------------------------------------|